



Specifications

**6497.000**

Volume 14 Litres
 External
 600x400x75mm
 Internal 555x355x70mm
 Weight 1.1 kg
 Colour grey
 Pallet unit: 136 pcs

**6499.000**

Volume 13 Litres
 External
 600x400x75mm
 Internal 555x355x65mm
 Weight 1.0 kg
 Colour grey
 Pallet unit: 132 pcs

**6497.500**

Volume 14 Litres
 Fixed dividers
 Size 600x400x75mm
 Weight 1.8 kg
 Colour grey
 Pallet unit: 136 pcs

**2360.000**


Volume 15 Litres
 External
 600x400x80mm
 Internal 570x370x70mm
 Weight 1.3 kg
 Colours grey, red
 Pallet unit: 128 pcs

**2360.720**


Volume 15 Litres
 External
 600x400x80mm
 Internal 570x370x70mm
 Weight 1.1 kg
 Colour grey
 Pallet unit: 128 pcs

**6470.750**

Volume 19 Litres
 External
 600x400x100mm
 Internal 555x355x95mm
 Weight 1.3 kg
 Colour grey
 Pallet unit: 96 pcs

**6471.750**

Volume 18 Litres
 External
 600x400x100mm
 Internal 555x355x90mm
 Weight 1.1 kg
 Colour grey
 Pallet unit: 96 pcs

**2361.000**

Volume 21 Litres
 External
 600x400x120mm
 Internal 560x360x115mm
 Weight 1.2 kg
 Colours grey, red
 Pallet unit: 84 pcs

**2361.720**

Volume 21 Litres
 External
 600x400x120mm
 Internal 560x360x108mm
 Weight 1.1 kg
 Colour grey
 Pallet unit: 84 pcs

**6472.750**

Volume 25 Litres
 External
 600x400x145mm
 Internal 555x355x140mm
 Weight 1.8 kg
 Colour grey
 Pallet unit: 64 pcs

**6474.750**


Volume 25 Litres
 External
 600x400x145mm
 Internal 555x355x140mm
 Weight 1.5 kg
 Colour brown
 Pallet unit: 64 pcs

**2362.000**

Volume 33 Litres
 External
 600x400x175mm
 Internal 560x360x170mm
 Weight 1.7 kg
 Colours grey, red
 Pallet unit: 56 pcs

**2362.720**

Volume 33 Litres
 External
 600x400x175mm
 Internal 560x360x165mm
 Weight 1.3 kg
 Colour grey
 Pallet unit: 56 pcs

**2364.000**



Volume 38 Litres
 External
 600x400x210mm
 Internal 560x360x205mm
 Weight 1.9 kg
 Colours grey, red
 Pallet unit: 44 pcs

**2364.720**

Volume 38 Litres
 External
 600x400x210mm
 Internal 560x360x200mm
 Weight 1.5 kg
 Colour grey
 Pallet unit: 44 pcs

**6479.750**

Volume 44 Litres
 External
 600x400x230mm
 Internal 555x355x225mm
 Weight 2.2 kg
 Colour grey
 Pallet unit: 40 pcs



Euro-Container Specifications

6476.750
Volume 55 Litres
External
600x400x280mm
Internal
560x360x275mm
Weight 2.7 kg
Colour grey
Pallet unit: 32 pcs



6478.750
Volume 55 Litres
External
600x400x280mm
Internal
560x360x275mm
Weight 2.1 kg
Colour brown
Pallet unit: 32 pcs




2366.750
Volume 56 Litres
External
600x400x300mm
Internal
560x360x295mm
Weight 3.0 kg
Colour grey
Pallet unit: 32 pcs



2367.750
Volume 60 Litres
External
600x400x320mm
Internal
560x360x315mm
Weight 2.9 kg
Colours grey, red
Pallet unit: 28 pcs



2367.720
Volume 60 Litres
External
600x400x320mm
Internal
560x360x305mm
Weight 2.4 kg
Colour grey
Pallet unit: 28 pcs



3640.750
Volume 80 Litres
External
600x400x410mm
Internal
555x355x400mm
Weight 3.7 kg
Colours grey, red
Pallet unit: 20 pcs



3640.720
Volume 80 Litres
External
600x400x410mm
Internal
555x355x400mm
Weight 2.8 kg
Colour brown
Pallet unit: 20 pcs



2368.750
Volume 87 Litres
External
600x400x440mm
Internal
575x375x420mm
Weight 3.7 kg
Colours grey, red
Pallet unit: 20 pcs

2368.720
Volume 87 Litres
External
600x400x440mm
Internal
575x375x420mm
Weight 3.6 kg
Colour grey
Pallet unit: 20 pcs



2360.820
Lid with rim and hooks
Size 600 x 400 mm
Weight 0.8 kg
Colour grey
Carton unit 17 pcs



5786.820
Lid with hooks
Size 600 x 400 mm
Weight 0.8 kg
Colour grey
Carton unit 15 pcs



7775.700 Dolly
Size 600 x 400
Weight 2.6 kg
Colours red, blue
Max load 250 kg
2 fixed and 2 castor wheels
Pallet unit: 60 pcs



7775.701 Dolly
Size 600 x 400
Weight 2.6 kg
Colour red
Max load 250 kg
4 castor wheels
Pallet unit: 60 pcs
7775.830 Handle for 7775



7773.830 Dolly
Size 600 x 400
Weight 5.0 kg
Colour galvanized steel
Max load 250 kg
2 fixed and 2 castor wheels
Pallet unit: 63 pcs



Black 920
Conductive material,
ESD