


Data sheet | Item number: 890-502

Strain relief housing; 2-pole; with locking clip; for 1 cable; 3.8 ... 8.2 mm; 30 mm; black

www.wago.com/890-502



Color: ■

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.



Item description

Strain relief housing WINSTA® MINI 2-pole

Realize the energy supply effortlessly: The strain relief housing from the WINSTA® MINI product line is the solution for error-free electrical installation. You can rely on the quality of WINSTA® components from WAGO for your electrical installation accessories too.

Where space is tight, our smallest pluggable connection system, WINSTA® MINI, conveniently displays its strengths. It is very compact, and, thanks to Push-in CAGE CLAMP® spring pressure connection technology, it also saves time, since the installation is low-maintenance and can be performed without screw connections. A range up to 32 mm can be used for the strip length.

WINSTA® MINI solutions for your electrical installation – maintenance-free

The WINSTA® Pluggable Connection System is perfectly tailored to the very strict requirements of building installation. It makes electrical installation pluggable, and consequently more efficient, more reliable, and error-free. Use of this pre-assembled system reduces assembly times and installation errors at the construction site. Now you can also reduce installation expenses without compromising quality and safety: The WINSTA® MINI accessory eliminates the need for servicing and prevents unnecessary downtime.

- consistent IP40 protection
- quick replacement of defective units during ongoing operation

Data

Connection data

Connection 1

Pole No.	2
Connectable sheathed cable diameter	3.8 ... 8.2 mm
Strip length (outer insulation)	32 mm

Physical data

Width	15.6 mm / 0.614 inch
Height	13.2 mm / 0.52 inch
Depth	44.8 mm / 1.764 inch

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.



Material data

Note on material data	Information on material data can be found here
Color	black
Insulation material	Polyamide (PA66)
Fire load	0.045 MJ
Weight	2.9 g

Environmental requirements


Processing temperature	-5 ... +40 °C
Continuous operating temperature	-35 ... +85 °C
Note on continuous operating temperature	Insulating parts for temperatures ≤ 105 °C

Commercial data

Product Group	20 (WINSTA)
PU (SPU)	50 Stück
Packaging type	box
Country of origin	DE
GTIN	4045454233310
Customs tariff number	39269097900

Approvals / Certificates

UL-Approvals

Logo	Approval	Additional Approval Text	Certificate name
	cURus Underwriters Laboratories Inc.	UL 1977	E45171

Downloads

Documentation

Bid Text

890-502 X81 - Datei	19-Feb-2019	xml 2.8 kB	Download
890-502	20-Nov-2014	doc	Download

Subject to changes. Please also observe the further product documentation!



doc - Datei

23.6 kB

CAD/CAE-Data

CAD data

2D/3D Models 890-502	URL	Download
----------------------	-----	----------

CAE data

EPLAN Data Portal 890-502	URL	Download
---------------------------	-----	----------

WSCAD Universe 890-502	URL	Download
------------------------	-----	----------

ZUKEN Portal 890-502	URL	Download
----------------------	-----	----------

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 890-502	URL	Download
Strain relief housing; 2-pole; with locking clip; for 1 cable; 3.8 ... 8.2 mm; 30 mm; black		

Installation Notes

Product family

WINSTA® MINI

[Show all products from the family](#)

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.