



ENGLISH

Datasheet

Stock No: 251-479

RS Pro 70 Piece Mechanical Tool Kit



Product Details

70 Piece Key, Bit & Driver Set

A 70 piece tool kit comprising of various and most used key, drivers and bits

Chrome vanadium steel Hex and Torx key wrenches

Chrome Molybdenum steel driver bits

Carbon steel driver shaft

Supplied in carry case



Kit Contents	
Ball End Hex Keys	Long: 1.5, 2, 2.5, 3, 4, 5, 6, 8, 10 mm
Tamperproof Torx Keys	Long: T10, T15, T20, T25, T27, T30, T40, T50
1/4in. Hex Shank 25mm	
Tamperproof Torx:	T8, T10, T15, T20, T25, T27, T30, T35, T40
Tamperproof Hex:	2.5, 3, 4, 5, 6, 7mm
Torq:	6, 8, 10 mm
Tri-Wing:	No.1, 2, 3, 4 ball
Security Spanner:	4, 6, 8, 10 mm
1/4in. Hex Shank 50mm	
Slotted:	3, 5, 6 mm
Phillips:	Ph1, Ph2, Ph3
Pozidriv:	Pz1, Pz2, Pz3
Tamperproof Torx:	T10, T15, T20, T25, T27, T30, T40
1/4in. Hex Magnetic Bit Holder	100mm
1/4in. Hex T Handle Bit Driver	x1
1/4in. Hex Bit Driver	Polypropylene
1/4in. Hex Stubby Bit Driver	Polypropylene

Standards

Power bits, bit holder and bit driver meet DIN-3126, bits meet ISO 8764 PH, DIN-2936, Camcar textron and ISO-2380 standards

Mixed Sets

Specifications

Set Type	Mechanical
Set Contents	Ball End Hexagon Keys Long: 1.5; 2; 2.5; 3; 4; 5; 6; 8; 10 mm; Tamperproof Torx Keys Long: T10; T15; T20; T25; T27; T30; T40; T50; 1/4 in Hexagon Shank: 25 mm; Tamperproof Torx: T8; T10; T15; T20; T25; T27; T30; T35; T40; Tamperproof Hexagon: 2.5; 3; 4; 5; 6; 7 mm; Torq: 6; 8; 10 mm; Tri-Wing Ball: #1; # 2; #3; #4; Security Spanner: 4; 6; 8; 10 mm; 1/4 in Hexagon Shank of 50 mm Slotted: 3; 5; 6 mm; 1/4 in Hexagon Shank of 50 mm Phillips: PH1; PH2; PH3; 1/4 in Hexagon Shank of 50 mm Pozidriv: PZ1; PZ2; PZ3; 1/4 in Hexagon Shank of 50 mm Tamperproof Torx: T10; T15; T20; T25; T27; T30; T40; 1/4 in Hexagon Magnetic 100 mm Bit Holder; 1/4 in Hexagon T Handle Bit Driver; 1/4 in Hexagon Bit Driver; 1/4 in Hexagon Stubby Bit Driver
Number of Pieces	70