


20M DIFFUSED ON BOARD


20 metres of uniform light output, powered from one end



Product Features


- Power required from one end only
- Uniform light output across the entire length of 20 metres
- Industrial grade adhesive backing tape
- Compatible with all dimming types
- Bespoke design and cutting service available
- IoT ready when paired with suitable controller
- 5 years warranty
- 50 metres reel also available

Part Code Structure



Specifications

Stock Code	0967-983	0908-955	0960-953	0958-962
Part Code	B7-DOB-24-504-10-20-20M	C0-DOB-24-504-10-20-20M	D0-DOB-24-504-10-20-20M	F0-DOB-24-504-10-20-20M
Input Voltage	24VDC	24VDC	24VDC	24VDC
Wattage	5.6W/m	5.6W/m	5.6W/m	5.6W/m
Lumen Output	504lm/m	513lm/m	579lm/m	577lm/m
Efficacy	89lm/W	92lm/W	104lm/W	104lm/W
CCT	2700K	3000K	4000K	6000K
LED/metre	504	504	504	504
Cut Points	41.67mm	41.67mm	41.67mm	41.67mm
CRI (Ra)	>90	>90	>90	>90
IP Rating	IP20	IP20	IP20	IP20
Dimensions	20000 x 10 x 1.9mm	20000 x 10 x 1.9mm	20000 x 10 x 1.9mm	20000 x 10 x 1.9mm




2700K



3000K



4000K



6000K



20M DIFFUSED ON BOARD

20 metres of uniform light output, powered from one end



Compatibility*



Suggested Drivers

Non-Dimmable


Up to 3m	Up to 5m	Up to 10m	Up to 20m
Power supplied from ONE end PCV2420	Power supplied from ONE end PCV2436-REV-A	Power supplied from ONE end PCV2475-REV-B	Power supplied from ONE end PCV24151

Mains Dimming


Up to 3m	Up to 5m	Up to 10m	Up to 20m
Power supplied from ONE end UVC2425TD-REV-A	Power supplied from ONE end UVC2450TD-REV-A	Power supplied from ONE end UVC24100TD-REV-A	Power supplied from ONE end UVC24150TD-REV-A

Mechanical Diagram

IP20



Connectors (10mm Tape)



Tape to Tape	Tape to Driver	Flexible Tape to Tape	Corner
15.6L x 11.6W x 3.3H mm	15.6L x 11.6W x 3.3H mm	15.6L x 11.6W x 3.3H mm	19x19L x 11.5W x 3.5H mm
10DC-2-20-5 (5 pcs)	10DC10-2-20-5 (5 pcs)	10DW10-2-20-5 (5 pcs)	10DCOR-2-20-5 (5 pcs)
10DC-2-20-30 (30 pcs)	10DC10-2-20-30 (30 pcs)	10DW10-2-20-30 (30 pcs)	10DCOR-2-20-30 (30 pcs)

* Product compatibility with other brands is shown for informational purposes only. All third-party company names and logos are trademarks of their respective owners and do not constitute an endorsement or partnership with our company.