


Technical Data



EXL AMBERGREASE **LONG LIFE BEARING GREASE**

EXL Ambergrease is a premium quality extremely stable multi-complex soap thickened grease designed to provide extended re-lubrication intervals in a wider range of non arduous and arduous working conditions. EXL Ambergrease is suitable for use in all types of anti-friction, sliding surfaces and plain bearings and has exceptional load carrying capacity which promotes long component life.

COST SAVING BENEFITS

1. Greatly extends lubrication intervals ensuring maximum cost savings in grease consumption.
2. Good water resistance and anti-corrosion agents protect and extend the working life of components.
3. Excellent EP performance provides protection against premature wear.
4. Versatile lubricant with a wide temperature range.

METHOD OF APPLICATION

EXL Ambergrease can be applied by hand, or by using a standard grease gun (400gm cartridges available), or via a central lubricating system capable of pumping an NLGI No. 2 Grease.

TECHNICAL DATA

Appearance	:	Red Soft Grease
NLGI Classification	:	2
Thickener	:	Lithium-Calcium Multi Complex
Base Fluid	:	Mineral Oil
Dropping Point (ASTM D2265)	:	>230°C
Water Washout (IP 215, ASTM D1264) @ 79°C	:	<2%
Dynamic Corrosion Resistance (IP 220)	:	0:0
Copper Corrosion (IP 112)	:	1a
Shell Four Ball Weld Load (IP 239)	:	800kgs
Mean Hertz Load	:	125kg
Timken OK Load (IP 236)	:	25kg (55lbs)
Operating Temperature Range	:	-30°C to 150°C

STORAGE

The product may be stored at normal ambient temperatures and has a shelf life of not less than 60 months with correct storage. Aerosols should always be stored below 50°C, away from direct heat and naked flame.

HEALTH AND SAFETY

Health and Safety sheet available separately.

MISREPRESENTATION ACT 1967

TRADE DESCRIPTIONS ACT 1968

The information given in this publication is based on our experience and reports from customers. There are many factors outside our control and knowledge which affect the use and performance of our products and for which reason no warranty is given, express or implied. Users should make their own tests to determine the applicability of such information or the suitability of any products for their own particular purposes. Statements concerning the use of the products described herein are not to be construed as recommending the infringement of any patent and no liability for infringement arising out of any such use is to be assumed.

CRC Industries UK Ltd, Wylds Road, Bridgwater, Somerset, TA6 4DD, UK.

Tel: +44 (0) 1278 727200

Fax: +44 (0) 1278 425644

Web: www.ambersil.com

E-mail: sales.uk@crcind.com