

# Product datasheet

Specifications



## MOUNTING PLATE VIGI NSX/CVS PLUGIN TOGGLE/ROT/MOT - 3P 250A HORIZONTAL WIDTH 650

LVS03413

EAN Code: 3606481874276

### Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT P cubicle
installation description	Cubicle - width 650 mm depth 400 mm
Installed device	<p>EasyPact: fixed CVS100...160 without earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>EasyPact: fixed CVS250 without earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: fixed NSX100...160 without earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: fixed NSX250 without earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>EasyPact: fixed CVS100...160 with earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>EasyPact: fixed CVS250 with earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: fixed NSX100...160 with earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: fixed NSX250 with earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: fixed NSX100...160 without earth leakage protection - control: motor mechanism - horizontal installation</p> <p>ComPact: plug-in NSX100...160 without earth leakage protection - control: toggle - horizontal installation</p> <p>ComPact: fixed NSX250 without earth leakage protection - control: motor mechanism - horizontal installation</p> <p>ComPact: plug-in NSX250 without earth leakage protection - control: toggle - horizontal installation</p> <p>ComPact: plug-in NSX100...160 without earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: plug-in NSX100...160 without earth leakage protection - control: motor mechanism - horizontal installation</p> <p>ComPact: plug-in NSX250 without earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: plug-in NSX250 without earth leakage protection - control: motor mechanism - horizontal installation</p> <p>ComPact: plug-in NSX100...160 with earth leakage protection - control: toggle - horizontal installation</p> <p>ComPact: fixed NSX100...160 with earth leakage protection - control: motor mechanism - horizontal installation</p> <p>ComPact: plug-in NSX100...160 with earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: plug-in NSX100...160 with earth leakage protection - control: motor mechanism - horizontal installation</p> <p>ComPact: plug-in NSX250 with earth leakage protection - control: toggle - horizontal installation</p> <p>ComPact: fixed NSX250 with earth leakage protection - control: motor mechanism - horizontal installation</p> <p>ComPact: plug-in NSX250 with earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: plug-in NSX250 with earth leakage protection - control: motor mechanism - horizontal installation</p>

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>Poles description</b>	1 x 3P: fixed CVS100...160 horizontal installation 1 x 3P: fixed CVS250 horizontal installation 1 x 3P: fixed NSX100...160 horizontal installation 1 x 3P: fixed NSX250 horizontal installation 1 x 3P: plug-in NSX100...160 horizontal installation 1 x 3P: plug-in NSX250 horizontal installation
<b>Number of vertical modules [50 mm]</b>	3 module(s): CVS100...160 without earth leakage protection , direct in 650 mm Widecubicle 3 module(s): CVS250 without earth leakage protection , direct in 650 mm Widecubicle 3 module(s): NSX100...160 without earth leakage protection , direct in 650 mm Widecubicle 3 module(s): NSX250 without earth leakage protection , direct in 650 mm Widecubicle 3 module(s): CVS100...160 with earth leakage protection , direct in 650 mm Widecubicle 3 module(s): CVS250 with earth leakage protection , direct in 650 mm Widecubicle 3 module(s): NSX100...160 with earth leakage protection , direct in 650 mm Widecubicle 3 module(s): NSX250 with earth leakage protection , direct in 650 mm Widecubicle
<b>Standards</b>	IEC 61439-2
<b>Product certifications</b>	ASTA

## Complementary

<b>Material</b>	Sheet steel
<b>Protective treatment</b>	Electrophoresis treatment and hot-polymerised polyester epoxy powder
<b>Surface finish</b>	Textured Matt
<b>Colour</b>	White (RAL 9003)
<b>Width</b>	650 mm
<b>Height</b>	200 mm
<b>Net weight</b>	2.015 kg

<b>Functional unit</b>	650 mm 400 mm PrismaSeT P cubicle EasyPact CVS100...160 without fixed direct front rotary handle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle EasyPact CVS250 without fixed direct front rotary handle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX100...160 without fixed direct front rotary handle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX100...160 without fixed motor mechanism horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX100...160 without plug-in direct front rotary handle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX100...160 without plug-in motor mechanism horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX100...160 without plug-in toggle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX250 without fixed direct front rotary handle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX250 without fixed motor mechanism horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX250 without plug-in direct front rotary handle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX250 without plug-in motor mechanism horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX250 without plug-in toggle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle EasyPact CVS100...160 with fixed direct front rotary handle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle EasyPact CVS250 with fixed direct front rotary handle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX100...160 with fixed direct front rotary handle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX100...160 with fixed motor mechanism horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX100...160 with plug-in direct front rotary handle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX100...160 with plug-in motor mechanism horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX100...160 with plug-in toggle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX250 with fixed direct front rotary handle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX250 with fixed motor mechanism horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX250 with plug-in direct front rotary handle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX250 with plug-in motor mechanism horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX250 with plug-in toggle horizontal 3P 1 direct 3 12.5 mm
------------------------	--

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	3.200 cm
<b>Package 1 Width</b>	15.000 cm
<b>Package 1 Length</b>	57.000 cm
<b>Package 1 Weight</b>	2.092 kg
<b>Unit Type of Package 2</b>	S35
<b>Number of Units in Package 2</b>	5
<b>Package 2 Height</b>	15.000 cm
<b>Package 2 Width</b>	40.000 cm
<b>Package 2 Length</b>	60.000 cm
<b>Package 2 Weight</b>	11.160 kg
<b>Unit Type of Package 3</b>	P12
<b>Number of Units in Package 3</b>	120

---

<b>Package 3 Height</b>	105.000 cm
<b>Package 3 Width</b>	80.000 cm
<b>Package 3 Length</b>	120.000 cm
<b>Package 3 Weight</b>	265.040 kg

---

## **Contractual warranty**

---

<b>Warranty (in months)</b>	18
-----------------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

[Environmental Disclosure](#)

[Product Environmental Profile](#)

## Use Better



### Materials and Substances

Packaging made with recycled cardboard

Yes

Packaging without single use plastic

No

[EU RoHS Directive](#)

Compliant with Exemptions

SCIP Number

4758f26b-dbf8-498a-a5c2-4de140d6aa9a

REACH Regulation

[REACH Declaration](#)

Halogen-free status

Halogen free plastic parts product

PVC free

Yes

Silicone-free

Yes

## Use Longer



### Lifetime extension

Repair

No

## Use Again



### Repack and remanufacture

End of life manual availability

No need of specific recycling operations


Take-back

No

Technical Illustration

Dimensions

---



- All dimensions are approximate and are in  
- Also see technical documentation.