

A792 - Needle Resistant Glove

Collection: Specialist Gloves

Range: Hand Protection

Materials: Nylon, Mesh Wire, Polyurethane, Elastic, PVC

Outer Carton: 48

Product information

Experience unparalleled protection against needles and sharp objects with our advanced glove. The palm boasts an impressive level 5 puncture resistance, while the fingers provide level 3 protection. But that's not all - our glove achieves level 1 protection in the challenging fourchette area which is typically very difficult to protect. With its textured finish, it guarantees superior grip and dexterity in any conditions. Achieving the pinnacle of dexterity, level 5, this glove empowers you to tackle intricate tasks effortlessly. Outstanding cut protection level F.

Specialist Gloves

The Portwest Pro range is a combination of highly specialised gloves which have been designed for very specific tasks. The use of these gloves with the right task will perform better than any other glove which has been designed for more general purposes.

Hand Protection

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwests' extensive range of Hand Protection products....

Standards

EN ISO 21420: 2020 Dexterity 5

EN 388: 2016 + A1: 2018 (3X24F)

ASTM F2878:2019 Level 5

ANSI/ISEA 105: 2016 PUNCTURE Level (5)

ANSI/ISEA 105: 2016 CUT Level (A9)



Features

- Level 5 puncture resistance against hypodermic needles
- Increased puncture resistance properties
- Reinforcement between the fingers to protect the vulnerable area of the hand
- Textured finish provides enhanced fingertip grip and dexterity in both wet and dry conditions
- Achieves the highest level of dexterity level 5
- Level F cut resistance
- Excellent for jobs requiring high dexterity
- New style
- CE certified
- UKCA marked
- Retail tag which aids presentation for retail sales



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

A792 - Needle Resistant Glove Commodity Code: 6116930000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
Bracetown Business Park
D15 YN2P, Ireland
Cert No: 2777/25072-01/E00-00

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
A792BKYS	Black/Yellow	57.0	35.0	25.0	0.1800	0.0499	5036108415397	15036108900944
A792BKYM	Black/Yellow	57.0	35.0	25.0	0.1980	0.0499	5036108415380	15036108900937
A792BKYL	Black/Yellow	57.0	35.0	25.0	0.2100	0.0499	5036108415373	15036108900920
A792BKYXL	Black/Yellow	57.0	35.0	25.0	0.2250	0.0499	5036108415403	15036108900951
A792BKYXXL	Black/Yellow	57.0	35.0	25.0	0.2410	0.0499	5036108415410	15036108900968