



1" short hexagonal impact sockets in mm

NM-....

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:56:30





DESCRIPTION

1" short hexagonal impact sockets in mm

Sockets designed to resist the force transmitted by impact tools (screwdrivers, electric or air impact wrenches) used in the automotive or other industries.

Ring and pin locking.

Very high wear resistance.

Burnished finish.

STANDARDS / DIRECTIVES

NF ISO 1711-1, NF ISO 1174-2, NF ISO 2725-2

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France


RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,¸

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:56:30



SPECIFIC DATA



Sales reference	Weight (g)	H (mm)	d (mm)	D (mm)	P (mm)	A (mm)	Guarantee
NM-30	640	62	54	49	22	30	O
NM-42	790	68	54	64	24	42	O
NM-80	2160	102	86	111.50	45	80	O
NM-24	610	58	54	41.5	17	24	O
NM-35	750	66	54	55	22	35	O
NM-55	1210	84	54	80	36	55	O
NM-77	2750	102	86	108	45	77	O
NM-27	630	60	54	45	19	27	O
NM-58	1500	84	54	84	36	58	O
NM-33	700	63	54	52.50	22	33	O
NM-60	1385	88	54	86.50	38	60	O
NM-75	1865	102	86	105	45	75	O
NM-29	620	62	54	47.50	22	29	O

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:56:30



NM-65	1700	92	54	92.50	38	65	O
NM-70	1590	96	54	99	40	70	O
NM-34	700	63	54	54	22	34	O
NM-54	1300	80	54	79	32	54	O
NM-41	845	68	54	62.50	24	41	O
NM-46	1612	72	54	69	26	46	O
NM-32	535	63	54	51.50	22	32	O
NM-90	4640	108	86	124	50	90	O
NM-22	600	58	54	39	17	22	O
NM-38	800	66	54	59	22	38	O
NM-50	1015	76	54	74	28	50	O
NM-21	530	58	54	37.50	17	21	O
NM-85	3000	106	86	117.50	50	85	O
NM-36	710	66	54	56.50	22	36	O
NM-23	600	58	54	40	17	23	O

Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

[>> Find out more](#)

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:56:30

