

Spring clamps

- Long tapered nose for hard to reach spaces
- Ergonomic 2-component handle designed for comfort and a firm grip
- Soft-touch pads for a non-marring grip



Clippix® needle nose plastic spring clamps (XCL)

BESSEY® Product #	Throat Depth Inches	Clamping Capacity Inches	Approx. Weight Pounds	Case qty.
XCL2	2	2	.04	12
XCL2-Set (2xXCL2)	2	2	.08	24
XCL5	4	3	.07	8

- Made from durable, lightweight polyamide
- Ergonomic 2-component handle designed for comfort and a firm grip
- Light duty spring clamps



Clippix® (XC) plastic spring clamps - Premium

BESSEY® Product #	Throat Depth Inches	Clamping Capacity Inches	Approx. Weight Pounds	Case qty.
XC1	3/4	3/4	0.02	96
XC2	1 1/8	1	0.04	20
XC3	1 1/2	1 3/4	0.11	36
XC5	1 15/16	2	0.26	20
XC7	2 3/4	3	0.46	10

- Light duty spring clamps for home or shop



NEW Clippix® (XC) plastic spring clamps - Econo

BESSEY® Product #	Throat Depth Inches	Clamping Capacity Inches	Approx. Weight Pounds	Case qty.
XC1-2	3/4	3/4	0.02	72
XC2-2	1 1/8	1	0.06	48
XC5-2	1 1/2	2	0.26	48
XC7-2	2 3/4	3	0.39	16

- Light duty spring clamps for home or shop
- 4 popular sizes, conveniently packaged in a mesh bag



Plastic spring clamp set

BESSEY® Product #	Includes	Approx. Weight Pounds	Case qty.
XC-14PC	2 x 3" clamps 2 x 2" clamps 4 x 1" clamps 6 x 3/4" clamps	2.06	4

- Heavy duty resin construction with pivoting jaw
- Ratcheting mechanism – quick action, quick release



Ratcheting spring clamps, deep reach (XCRU)

BESSEY® Product #	Throat Depth Inches	Clamping Capacity Inches	Approx. Weight Pounds	Case qty.
XCRU3	2	2	0.50	12
XCRU5	4	4	0.75	12

- Heavy duty resin construction with pivoting jaw
- Ratcheting mechanism – quick action, quick release



Ratcheting spring clamp set (XCR)

BESSEY® Product #	Includes	Approx. Weight Pounds	Case qty.
XCR-4PC	4 x 2" clamps	2.20	6

- Vinyl tips and handles prevent marring
- Heavy duty springs for firm grip
- Nickel plating resists corrosion



Steel spring clamps (XM)

BESSEY® Product #	Throat Depth Inches	Clamping Capacity Inches	Approx. Weight Pounds	Case qty.
XM3	1	1 1/4	0.17	48
XM5	2	2 1/4	0.40	24
XM7	3	3 5/16	0.80	6
XM10	4	5	1.00	6



* All items come packed in retail ready full colour shelf display - must order case qty to get shelf display.