

SIA10

Socket interface adaptor



- **Allows sockets to be tested without disassembly**
- **Prevents damage to connections**
- **Reduces test time**
- **Decoration remains in tact**
- **Colour coded for simplicity of use**
- **Makes testing easy where access to socket is limited**
- **Remains safe if left inadvertently connected to live supply**

DESCRIPTION

The Megger socket interface adaptor is the safe solution when you want to test insulation and continuity at a UK BS1363 13 A 3-pin power socket., as disassembly of the socket and exposure of live conductors is eliminated. Full flexibility of connection is enabled by three separate 4 mm plugs capable of connecting to any input point of the tester, so reducing the time taken to test.

Plugs are colour coded for easy identification, and configuration changes are done at the tester, so difficult access socket locations such as under desks or within cupboards are no longer a problem. This adaptor is ideal for use when the electrical outlet is in a tight space and working directly into the back of a socket would be difficult.

A further application is Phase-Earth or Phase-Neutral loop or impedance testing without socket disassembly.

The added benefit of the Socket Interface Adaptor (6220-810) is the security of mind, knowing that should the adaptor get forgotten and left on site there is no potential hazard for your clients or their children.

SPECIFICATIONS

CONNECTIONS

Test end: UK BS1363 13 A 3-pin

Instrument end: Colour coded 4 mm plug with safety shroud

Voltage: 0 V to 600 V dc/ac (0/1kHz)

Operating Temperature: -10°C to +50°C

Safety rating

IEC/EN61010-1:2001-02 over voltage Cat II 300 V

Length: 1.48m

Weight: 230gms

Warranty: 1 year

ORDERING INFORMATION

Item (Qty)	Order No.	Also available	Order No.
Socket interface adaptor	6220-810	Socket tester	1000-211
		30 m extension test lead and spool	1000-215
		50 m extension test lead and spool	1000-217

UK
Archcliffe Road Dover
CT17 9EN England
T +44 (0) 1304 502101
F +44 (0) 1304 207342

UNITED STATES
4271 Bronze Way
Dallas TX 75237-1019 USA
T 800 723 2861 (USA only)
T +1 214 333 3201
F +1 214 331 7399

OTHER TECHNICAL SALES OFFICES
Norristown USA, Sydney AUSTRALIA,
Toronto CANADA, Trappes FRANCE,
Kingdom of BAHRAIN, Mumbai INDIA,
Johannesburg SOUTH AFRICA and
Conjure THAILAND.

Registered to ISO 9001:2000 Cert. Q 09290
Registered to ISO 14001:1996 Cert. EMS 61597

SIA10_DS_en_V01

www.megger.com
Megger is a registered trademark