

PMT (10X38) OG - Insert label



0831088

<https://www.phoenixcontact.com/gb/products/0831088>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marking label for conveyed fluids, for equipping CARRIER-PMP (110x38), CARRIER/L-PMP (110x38), and CARRIER-PMP-ENCLOSED (110x38) according to DIN 2403



Commercial data

Item number	0831088
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BG261Z
Product key	BG261Z
Catalog page	Page 364 (C-3-2019)
GTIN	4046356941211
Weight per piece (including packing)	0.593 g
Weight per piece (excluding packing)	0.593 g
Customs tariff number	39199080
Country of origin	DE

PMT (10X38) OG - Insert label



0831088

<https://www.phoenixcontact.com/gb/products/0831088>

Technical data

Product properties

Product type	Labeled systems marker
Area of application	Identification of flow substances according to DIN 2403

Marking

Number of individual labels	1
Number of individual labels per row	1

Dimensions

Width	10 mm
Length	38 mm
Material strength	1.10 mm

Material specifications

Color	orange (RAL 2003)
Material	PVC
Components	Free from silicone and cadmium

Environmental and real-life conditions

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	10 °C ... 30 °C
Recommended humidity (storage/transport)	40 % ... 70 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	12 months

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	latching
---------------	----------

PMT (10X38) OG - Insert label



0831088

<https://www.phoenixcontact.com/gb/products/0831088>

Classifications

ECLASS

ECLASS-11.0	27281104
ECLASS-12.0	27281104
ECLASS-13.0	27281104

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

PMT (10X38) OG - Insert label



0831088

<https://www.phoenixcontact.com/gb/products/0831088>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

info@phoenixcontact.co.uk