



## 3/8" SOCKET SET 12 PT TT1 16 PIECES

- Deep 12 point bi-hexagon sockets
- Chrome vanadium satin finish sockets
- Designed and manufactured to DIN3120/3124 and ISO2725
- Organised in a tool tray module size 1 (TT1)

Socket Set 3/8" Drive 12 Point 16 Pieces TT Tray

### General information

**Country of origin:** Taiwan  
**Barcode:** 5020385011489  
**Tarriff code Europe:** 8204200000  
**ECCN US:** EAR99  
**ETIM:** EC002209  
**UNSPSC:** 27111703

### Dimensions

**Net weight (g):** 1611  
**Width (mm):** 142  
**Depth (mm):** 265  
**Height (mm):** 50

### Attributes

**Product type:** Sockets & Accessories Sets  
**Certificates:** N/A  
**Number of pieces:** 16  
**Drive:** 3/8"  
**Socket type:** Deep, 12-point  
**Unit of measurement:** Metric  
**Inlay material:** PS  
**Type of set:** TT1

### Features



Technical changes and errors may occur. 01-08-2024 19:49



**DESIGNED IN SWEDEN**

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3  
 441 39 Alingsås, Sweden

# ADDITIONAL IMAGES



WWW.TENGOOLS.COM



# LIST OF CONTENTS



**TT381612** 3/8" Socket Set 12 pt TT1 16 Pieces

- M38060712-C** 3/8" Deep Socket 12 pt Metric 7 mm
- M38060812-C** 3/8" Deep Socket 12 pt Metric 8 mm
- M38060912-C** 3/8" Deep Socket 12 pt Metric 9 mm
- M38061012-C** 3/8" Deep Socket 12 pt Metric 10 mm
- M38061112-C** 3/8" Deep Socket 12 pt Metric 11 mm
- M38061212-C** 3/8" Deep Socket 12 pt Metric 12 mm
- M38061312-C** 3/8" Deep Socket 12 pt Metric 13 mm
- M38061412-C** 3/8" Deep Socket 12 pt Metric 14 mm
- M38061512-C** 3/8" Deep Socket 12 pt Metric 15 mm
- M38061612-C** 3/8" Deep Socket 12 pt Metric 16 mm
- M38061712-C** 3/8" Deep Socket 12 pt Metric 17 mm
- M38061812-C** 3/8" Deep Socket 12 pt Metric 18 mm
- M38061912-C** 3/8" Deep Socket 12 pt Metric 19 mm
- M38062012-C** 3/8" Deep Socket 12 pt Metric 20 mm
- M38062112-C** 3/8" Deep Socket 12 pt Metric 21 mm
- M38062212-C** 3/8" Deep Socket 12 pt Metric 22 mm