


Thomas & Betts


Cable Tie Mounting Bases



Self-Riveting Base

| Bulk Cat. No. | Mounting Hole Size | Maximum Tie Width Accom. | Width (in.) | Length (in.) | Material | Bulk Pkg. |
|---------------|--------------------|--------------------------|-------------|--------------|--------------------|-----------|
| TC116-TB | .146 | .190 | .500 | .750 | Nylon 6/6 (Red) | 1000 |
| TC118-TB | .169 | .190 | .500 | .750 | Nylon 6/6 (Blue) | 1000 |
| TC120 | .196 | .190 | .500 | .750 | Nylon 6/6 (Yellow) | 1000 |

Knock-in mounting base TC116-TB, TC118-TB, TC120—firmly locks into position when projecting pin is knocked into hollow peg. Slip tie under base and tie as usual.




TC115

Ty-Rap® Mounting Blocks

| Bulk Cat. No. | Mounting Bolt Size | Maximum Tie Width Accom. | Width (in.) | Length (in.) | Bulk Pkg. |
|---------------|--------------------|--------------------------|-------------|--------------|-----------|
| TC115-TB | #10 | .190 | .469 | 1.00 | 1000 |

Mounting blocks permit vertical stacking and can be used in any direction.




TC376

Ty-Rap® Stand-Off Brackets

| Bulk Cat. No. | Maximum Tie Width Accom. | Width (in.) | Length (in.) | Bulk Pkg. |
|---------------|--------------------------|-------------|--------------|-----------|
| TC375 | .190 | .750 | 3.65 | 100 |
| TC376 | .190 | .670 | 1.75 | 100 |


These brackets permit bundles to be mounted on either side. They also serve as means to raise bundles off the surface.



Right-Angle Bundle Support

| Bulk Cat. No. | Maximum Tie Width Accom. | Width (in.) | Length (in.) | Bulk Pkg. |
|---------------|--------------------------|-------------|--------------|-----------|
| TC109 | .190 | .563 | .438 | 200 |
| TC106 | .301 | 1.000 | 1.000 | 1000 |

This style meets Military Specification requirements as a support at holes in bulkheads and walls.



Aluminum Siding Clip

| Cat. No. | Wire Accommodation | Bulk Pkg. |
|----------|--------------------------------------|-----------|
| TC201 | 1/8" dia. wire (2 pair station wire) | |

Material:

- Transparent – Color and texture of siding shows through.
- Material – Weather resistant grade polycarbonate.
- Designed to accommodate PITTSBURG INTERLOCK metal siding.
- Accommodates wires both vertically and/or horizontally.
- Provision for utilizing Ty-Rap® cable ties to secure large diameter bundles.

Thomas & Betts