

Features

- Conical cartridge rolls are ideal for removing burrs, smoothing edges, grinding welds, and removing machining marks in hard-to-reach areas such as corners, holes or moulds.
- Its design ensures continuous release of new abrasive grains as the outer layer wears, allowing for precise control of the grinding process.
- Available in various sizes and grits.
- For use with handheld machines (straight grinders or flexible shaft grinders) after mounting on a suitable mandrel.
- Applications:
 - Deburring
 - Cleaning
 - Finishing operations

RS PRO Sanding Drums

RS Stock No.: 0768296, 0768298, 0768300, 0768303



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Conical cartridge rolls are intended for grinding in hard-to-reach places and for deburring castings. They have a multilayer structure; new abrasive grain is exposed when the top layer is worn down. To be used with a straight grinder or drill. Suitable for carbon and stainless steel, aluminium alloys/non-ferrous metals.

General Specifications

Dimensions (Diameter D x Length L x Hole H)	13 mm x 38 mm x 3 mm
Grain Type	Aluminium Oxide (A/O)
Material (Backing/Coating)	Heavy Cotton Cloth / Close coat

Mechanical Specifications

Recommended Mandrel	0768256
Recommended Speed	11,000 min ⁻¹

Grits vs RS Pro Codes

Grits	RS Pro Codes
P60	0768296
P80	0768298
P120	0768300
P150	0768303

Similar Products

Stock No.	Brand	Product Name	Size	Grain Type	Grit	Suitable mandrel
0768152	RS PRO	Conical Cartridge Roll	10x25x3	Aluminium Oxide	60	0768254

0768155	RS PRO	Conical Cartridge Roll	10x25x3	Aluminium Oxide	80	0768254
0768156	RS PRO	Conical Cartridge Roll	10x25x3	Aluminium Oxide	120	0768254
0768158	RS PRO	Conical Cartridge Roll	10x25x3	Aluminium Oxide	150	0768254
0768160	RS PRO	Conical Cartridge Roll	10x25x3	Aluminium Oxide	60	0768256
0768162	RS PRO	Conical Cartridge Roll	10x38x3	Aluminium Oxide	80	0768256
0768164	RS PRO	Conical Cartridge Roll	10x38x3	Aluminium Oxide	120	0768256
0768167	RS PRO	Conical Cartridge Roll	10x38x3	Aluminium Oxide	150	0768256
0768286	RS PRO	Conical Cartridge Roll	13x25x3	Aluminium Oxide	60	0768254
0768288	RS PRO	Conical Cartridge Roll	13x25x3	Aluminium Oxide	80	0768254
0768291	RS PRO	Conical Cartridge Roll	13x25x3	Aluminium Oxide	120	0768254
0768293	RS PRO	Conical Cartridge Roll	13x25x3	Aluminium Oxide	150	0768254