



Chemical protection

# ULTRANITRIL 381

Frequent contact | ultra-comfort wear

## Maximum comfort and chemical protection



CHEMICAL PROTECTION  
**TYPE A**



DEXTERITY  
EN ISO 21420:  
5/5

### SPECIFIC ADVANTAGES



#### Thermal protection

- Added comfort and thermal insulation, due to the cotton-knit lining



#### Comfort

- Extremely supple, due to the unique Mapa multi-layer process



#### Productivity

- Good grip on slippery objects, due to the embossed texture



#### Additional benefits

- Available in vending machine packaging



#### Care for the environment

- Plastic packaging optimized, Recycled packaging
- Recycled material in the packaging: 30 %

### INDUSTRIES

- Automotive/mechanical industry
- Chemical industry
- Other industries
- Agriculture sector

### APPLICATIONS

- Spray mixtures preparation
- Pesticides handling
- Tank filling
- Application & spreading of pesticides
- Pesticides waste management
- Treatment equipment cleaning
- Chemical product blending
- Handling drums of chemical products
- Manipulating valves
- Laboratory tests





Chemical protection

# ULTRANITRIL 381

Frequent contact | ultra-comfort wear

## LEGENDS



**EN ISO 374-1** **CHEMICAL RISKS**

**TYPE A**

A: Methanol  
J: n-Heptane  
K: Sodium hydroxide 40%  
L: Sulphuric acid 96%  
O: Ammonia 25%  
P: Hydrogen peroxide 30%  
T: Formaldehyde 37%

**PROTECTION FROM PESTICIDES**

G2: Diluted & concentrated pesticides / Mechanical risk

ISO 18889

**EN ISO 374-5** **MICRO-ORGANISMS**

Protection against bacteria and fungi

## PRODUCT DETAILS

Interior finish	Textile support Mapa Technology
Exterior finish	Embossed texture
Material	Nitrile
Cuff characteristic	Feston Cuff
Colour.s	Green
Length (cm)	36
Thickness (mm)	0.95
European sizes	7 8 9 10 11
Surface resistance according to EN1149-1 (Value in palm area at 25% relative humidity)	7.6E+10 Ω
Vertical resistance according to EN1149-2 (Value in palm area at 25% relative humidity)	2.9E+10 Ω

## LOGISTIC DETAILS

Packaging	12 pairs/bag 72 pairs/carton
-----------	---------------------------------

## LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/08/18/1663
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France