

HCS-KIT-C MINI 1W 9V C C 7035 - Electronics housing



1343037

<https://www.phoenixcontact.com/in/products/1343037>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Handheld housing, C-Mini, light gray, consisting of two half shells, screws. Front 1.1 mm recessed, closed, battery compartment cover and battery contacts for 9 V battery

Your advantages

- Suitable for handheld devices
- Easy integration of LCD displays and membrane keypads
- Ergonomic straight or staggered housing design
- Fast mounting, thanks to the modular design

Commercial data

Item number	1343037
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	ACFABK
GTIN	4063151653095
Weight per piece (including packing)	95.1 g
Weight per piece (excluding packing)	95.1 g
Customs tariff number	84879090
Country of origin	DE

HCS-KIT-C MINI 1W 9V C C 7035 - Electronics housing



1343037


<https://www.phoenixcontact.com/in/products/1343037>

Technical data

Product properties

Product type	Complete housing
Housing type	Handheld housing
Housing series	HCS
Type	straight
Ventilation openings present	no
Battery compartment	9 V

Dimensions

Dimensional drawing	
Width	70.5 mm
Height	110 mm
Depth	26 mm
Dimensions	60.5 mm x 100 mm x 1.1 mm (Recessed area on front)

Material specifications

Color (Housing)	light gray (RAL 7035)
Flammability rating according to UL 94	V0
CTI according to IEC 60112	$400 \leq CTI < 600$
Insulating material	II
Housing material	ABS
Surface characteristics	untreated

Environmental and real-life conditions

Degree of protection (IP code)

Specification	IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08
---------------	---

Ambient conditions

Max. IP code to attain	IP40
Ambient temperature (operation)	-40 °C ... 80 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 80 °C
Relative humidity (storage/transport)	95 %


HCS-KIT-C MINI 1W 9V C C 7035 - Electronics housing

1343037

<https://www.phoenixcontact.com/in/products/1343037>

Drawings

Dimensional drawing



Schematic representation – for additional information, see product range drawing in the Download Center

HCS-KIT-C MINI 1W 9V C C 7035 - Electronics housing



1343037
<https://www.phoenixcontact.com/in/products/1343037>

Classifications

ECLASS

ECLASS-13.0	27190102
-------------	----------

ETIM

ETIM 9.0	EC001031
----------	----------

HCS-KIT-C MINI 1W 9V C C 7035 - Electronics housing



1343037

<https://www.phoenixcontact.com/in/products/1343037>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	df805e4c-d3fa-49e6-b885-bf68efdcf4bd

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in