

5980U/BIKE-M
Assortment of 106 bicycle tools

		art.
	059801050	5980U/BIKE-M

- n. 16 **42:** combination wrenches 6-7-8-9-10-11-12-13-14-15-16-17-18-19-20-21 mm
- n. 8 **96T:** offset hexagon key wrenches $\square$ 2-2,5-3-4-5-6-7-8 mm
- n. 5 **97TTX:** drivers for Torx® head screws, with handles $\odot$
TX10-TX15-TX20-TX25-TX30
- n. 1 **1084:** Heavy-duty diagonal cutting nippers ∇ 160 mm
- n. 1 **1150:** combination pliers bright chrome-plated $\equiv$ 160 mm
- n. 1 **1166:** Extra-long needle nose pliers $\bullet$ 160 mm
- n. 6 **1201E:** screwdriver for slotted head screws $\bullet$
2,5x50-3x75-4x100-5,5x125-6,5x150-8x200 mm
- n. 1 **1201EN:** screwdriver for slotted head screws, extra-short series $\bullet$ 4x30 mm
- n. 4 **1202E:** screwdriver for cross head Phillips® screws $\oplus$
PH0x60-PH1x80-PH2x100-PH3x150 mm
- n. 1 **1202EN:** screwdriver for cross head Phillips® screws, extra-short series $\oplus$ 4,5x30 mm
- n. 12 **1207E/TX:** screwdrivers for Torx® head screws, with handles $\odot$
TX6-TX7-TX8-TX9-TX10-TX15-TX20-T25-TX27-TX30-TX40-TX45
- n. 1 **1253:** mains testing screwdriver $\bullet$
- n. 1 **1370:** engineer's hammer 300 g
- n. 1 **1390:** soft face hammer $\varnothing$ 35 mm
- n. 2 **35:** flat chisels, ribbed type 100-200 mm
- n. 1 **1719BMA...S5:** Set of 5 second-cut files, with handles 200 mm
- n. 1 **1692:** measuring tape 5 m
- n. 1 **1725CR:** mini hacksaw frame 250 mm
- n. 1 **1771:** snap - off blade utility knife 170 mm
- n. 1 **1771RL:** 18 mm snap-off spare blades (10 pieces) for utility knives 1771, 1771BM, 1771HD
- n. 1 **3932U:** professional chain tool compatible with chains from 5 to 11 speeds
- n. 1 **3935:** chain wear indicator
- n. 1 **3937:** missing link pliers
- n. 7 **3952:** simple cone wrench 13-14-15-16-17-18-19 mm
- n. 1 **3961 3,2:** spoke wrench, black, 3.2 mm $\square$ 3,2 mm
- n. 1 **3961 3,3:** spoke wrench, green, 3.3 mm $\square$ 3,3 mm
- n. 1 **3961 3,5:** spoke wrench, red, 3.5 mm $\square$ 3,5 mm
- n. 1 **3961U:** professional spoke wrench, 3.2 - 4.0 mm $\square$ 3,2-4,0 mm
- n. 1 **3969:** tyre lever
- n. 1 **3969K3:** kit with 3 tyre levers, made of plastic
- n. 1 **3973/1:** 16-notch bottom bracket removal socket 39 mm
- n. 1 **3973/2:** 16-notch bottom bracket removal socket 41 mm
- n. 1 **3973/3:** 16-notch bottom bracket removal socket 46 mm

