



## Open ring insert tool

**733/10**

Product no. **58231022**  
GTIN **4018754034437**  
Model **733/10 22**





### Label.

Open ring insert tool Size 22mm Tool holder 9 x 12

### Properties.

- bi-hex with AS-Drive profile
- for torque wrenches with interchangeable insert system
- special chromium over nickel plating, durable and chip-proof finish
- drop-forged, hardened, and cooled in an oil bath
- extremely strong, exceptionally durable

## Technical drawing.



## Technical attributes.

|                                    |           |
|------------------------------------|-----------|
| Width mm (b)                       | 39,5 mm   |
| Tool holder size [internal square] | 9 x 12 mm |
| Height mm (h)                      | 15 mm     |
| S                                  | 20 mm     |
| Size [mm]                          | 22 mm     |

## Logistics data.

|                       |                     |
|-----------------------|---------------------|
| Depth mm (IFS)        | 53                  |
| Width mm (IFS)        | 40                  |
| Height mm (IFS)       | 15                  |
| WEEE/ElektroG         | nicht ear-pflichtig |
| Length (packaged, mm) | 59                  |
| Width (packaged, mm)  | 43                  |

|          |       |                               |                     |
|----------|-------|-------------------------------|---------------------|
| <b>W</b> | 17 mm | <b>Height (packaging, mm)</b> | 16                  |
|          |       | <b>Volume (packaged, dm3)</b> | 0.040592 dm3        |
|          |       | <b>Product no.</b>            | 58231022            |
|          |       | <b>Weight (gross, kg)</b>     | 0,095               |
|          |       | <b>Weight PAP (kg)</b>        | 0,000               |
|          |       | <b>Weight PVC (kg)</b>        | 0,002               |
|          |       | <b>GTIN</b>                   | 4018754034437       |
|          |       | <b>Country of origin AWR</b>  | GERMANY             |
|          |       | <b>Region of origin</b>       | Nordrhein-Westfalen |
|          |       | <b>Customs tariff no.</b>     | 82041100            |
|          |       | <b>Packing standard</b>       | 1                   |
|          |       | <b>Weight (g)</b>             | 92 g                |

## Variants.

| Product no. | Model No. (ERP) | Description                                       | GTIN          |
|-------------|-----------------|---|---------------|
| 58231010    | 733/10 10       | Open ring insert tool Size 10mm Tool holder9 x 12 | 4018754034352 |
| 58231011    | 733/10 11       | Open ring insert tool Size 11mm Tool holder9 x 12 | 4018754034369 |
| 58231012    | 733/10 12       | Open ring insert tool Size 12mm Tool holder9 x 12 | 4018754034376 |
| 58231013    | 733/10 13       | Open ring insert tool Size 13mm Tool holder9 x 12 | 4018754034383 |
| 58231014    | 733/10 14       | Open ring insert tool Size 14mm Tool holder9 x 12 | 4018754034390 |
| 58231016    | 733/10 16       | Open ring insert tool Size 16mm Tool holder9 x 12 | 4018754085163 |
| 58231017    | 733/10 17       | Open ring insert tool Size 17mm Tool holder9 x 12 | 4018754034406 |
| 58231018    | 733/10 18       | Open ring insert tool Size 18mm Tool holder9 x 12 | 4018754034413 |
| 58231019    | 733/10 19       | Open ring insert tool Size 19mm Tool holder9 x 12 | 4018754034420 |
| 58231021    | 733/10 21       | Open ring insert tool Size 21mm Tool holder9 x 12 | 4018754085170 |
| 58231022    | 733/10 22       | Open ring insert tool Size 22mm Tool holder9 x 12 | 4018754034437 |
| 58231024    | 733/10 24       | Open ring insert tool Size 24mm Tool holder9 x 12 | 4018754034444 |

## GTIN.



## Accessories (for).



18200001  
Tool holder

**STAHLWILLE Eduard Wille GmbH**

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0

info@stahlwille.de · www.stahlwille.com

© STAHLWILLE Eduard Wille GmbH, Wuppertal