

USB-C Headphone Splitter, USB Type C Dual Headset Adapter w/Mic Input, USB C to 3.5mm Audio Adapter/Earphone Dongle, USB C to Audio Jack/Aux Output, 24-bit DAC

Product ID: USBC-AUDIO-SPLITTER



This USB Type-C Headphone Splitter enables two 3.5mm audio connections. The 3.5mm ports accept 4-pole 3.5mm TRRS connectors and support simultaneous stereo audio output and headset/microphone input. The adapter also features an integrated 2.75in (7cm) USB-C cable.

Connect two headsets to the same USB-C port. Microphone input is supported across both headsets, offering a convenient solution for team training and conferencing calls. The adapter supports dual CTIA or dual OMTP headset types allowing universal compatibility.

The USB-C headset dongle features built-in 24-bit Digital to Analog Converter (DAC). The DAC supports a sampling rate of up to 192kHz for uncompromising quality and performance.

The USB-C to dual-audio adapter is small and lightweight, perfect for professionals who are frequently on the go. It is the ideal solution for adding two 3.5mm audio jacks to a USB-C device.

This product is backed for 2 years, including free lifetime 24/5 multi-lingual technical assistance.

Certifications, Reports and Compatibility



Applications

Features

- **USB-C HEADPHONE SPLITTER** : Convert the USB C port on laptop/phone/tablet into two 3.5mm headphone jacks for high quality audio, mic and headset controls on both 3.5mm jacks; Ideal for team conferencing/meetings/presentations/training centers
- **HIGH PERFORMANCE**: USBC to dual-headphones dongle features built-in 24-bit Digital to Analog Converter (DAC) ensuring uncompromising quality and performance for Hi-Res audio with sampling rate up to 192kHz
- **COMPATIBILITY**: The USB Type-C audio adapter supports dual CTIA or dual OMTP headphones/headsets; Compatible with MacBook Pro/MacBook/MacBook Air/iPad/iPad Pro/iPad Air/Samsung Galaxy S/Galaxy Note/Google Pixel; Ideal use with high impedance headsets
- **COMPACT DESIGN**: The AUX adapter is compact and lightweight and features an attached 2.7in/7cm cable with strain relief for portability and flexibility
- **THE IT PRO'S CHOICE**: Designed and built for IT Professionals, this USB Type C earphone splitter is backed for 2 years, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	2 Years
Ports	2
Connector Plating	Aluminum
Cable Jacket Material	TPE - Thermoplastic Elastomers

Performance

Audio Specifications	16-bit depth at a sampling rate of 8~192kHz 24-bit depth at a sampling rate of 8~192kHz
----------------------	--

Connector(s)

Connector A	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)
Connector B	2 - 3.5 mm Audio

Environmental

Operating Temperature	0 to 70C (32 to 158F)
Storage Temperature	-10 to 70C (14 to 158F)
Humidity	5 to 90% RH

Physical Characteristics

Color	Black & Space Gray
-------	--------------------



Connector Style	Straight
Material	Aluminum
Cable Length	0.3 in [0.7 cm]
Cable OD	0.1 in [3.2 mm]
Product Length	4.5 in [11.4 cm]
Product Width	1.1 in [2.7 cm]
Product Height	0.3 in [8.0 mm]
Weight of Product	0.7 oz [19.0 g]

Packaging Information

Package Quantity	1
Package Length	3.5 in [9.0 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.3 in [8.2 mm]
Shipping (Package) Weight	0.7 oz [20.0 g]

What's in the Box

Included in Package	1 - USB Type-C to 2x 3.5mm Audio Adapter
---------------------	--

**Product appearance and specifications are subject to change without notice.*

