

Plug Kit, Common Core, 8P ✓ ACTIVE

Industrial RJ45 Variant 1

TE Part # 1954656-2

TE Internal #: 1954656-2

[View on TE.com >](#)



Connectors > Modular Jacks & Plugs > Circular RJ45 Connectors



Modular Jacks & Plugs Products: **RJ Type Jacks & Plugs**

Connector Contact Density: **Standard**

Modular Connector Style: **Plug**

Shielded: **No, Yes**

Performance Category: **Cat 5e**

Features

Product Type Features

Connectors & Connector Components Type	Connector
Modular Jacks & Plugs Products	RJ Type Jacks & Plugs
Modular Connector Style	Plug
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Connector Contact Density	Standard
---------------------------	----------

Body Features

Shield Plating Material	Nickel
Shield Material	Copper Alloy
Seal Material	Elastomer

Contact Features

Contact Mating Area Plating Material	Gold over Nickel
Contact Base Material	Copper Alloy

Housing Features

Housing Color	Black
Housing Material	Polyester

Dimensions

Wire Size	.129 mm ²
-----------	----------------------

Operation/Application



Shielded	No, Yes
----------	---------

Industry Standards

IP Rating	IP67
Performance Category	Cat 5e

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JAN 2019 (197)
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Also in the Series | [Industrial RJ45 Variant 1](#)



Circular Ethernet Hardware
(2)



Circular RJ45 Connectors
(22)



Modular Jack & Plug Caps
& Covers(2)



Modular Jack Filters(1)

Customers Also Bought



TE Part #1811689-1
Recptacle Kit,8 Pos
Shielded



TE Part #1546440-1
ETHERNET FIELD
ATTACHABL CONN



TE Part #1738611-1
PROTECTIVE COVER
ASSEMBLY



TE Part #1738607-1
KIT, PLUG, SOLID WIRE



TE Part #1828740-1
ASSEMBLY, PROTECTIVE
CAP




TE Part #1954637-1
Plug Kit,USB Series A



TE Part #1954643-1
Recpt Kit,Series A to
Series A



TE Part #2008618-1
Protective Cover Kit



TE Part #5-103945-9
2X10 MTE SHRD PIN SR
LTCH .100



TE Part #5-1437665-3
JC6-Q307-04=JC6
ASSEMBLY

Documents

Product Drawings

Plug Kit,Common Core,8P

English

CAD Files

Customer View Model

ENG_CVM_CVM_1954656-2_A.2d_dxf.zip

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_1954656-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1954656-2_A.3d_stp.zip](#)

English

Datasheets & Catalog Pages

[IP67_COMMON_CORE_CONNECTOR](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English