



Chemical protection

HARPON 326

Textile support | continuous wear



CHEMICAL PROTECTION
TYPE B

EN388



3141X

EN ISO 374-1



TYPE B
KPT

EN407



X2XXXX

CATEGORY 3



0334

DEXTERITY

EN ISO 21420:
5/5



Comfort and safety when gripping heavy, rough or slippery objects in food industry

SPECIFIC ADVANTAGES



Thermal protection

- Suitable for long-term wear, due to the comfort of a textile support and good thermal insulation



Durability

- Optimised service life: high resistance to abrasion



Productivity

- Reinforce grip for better handling



Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting

INDUSTRIES

- Food industry
- Fishing

APPLICATIONS

- Handling of fatty foods
- Oyster farming
- Fishing
- Fish-handling
- Handling fresh, slippery products



Chemical protection

HARPON 326

Textile support | continous wear

LEGENDS

EN388 **MECHANICAL HAZARDS**



PERFORMANCE LEVELS (X = NOT TESTED)

3	1	4	1	X	
0-4	0-5	0-4	0-4	A-F	P

Impact protection (optional)

Cut resistance according to ISO 13997

Puncture resistance

Tear resistance

Blade cut resistance

Abrasion resistance

EN407 **THERMAL RISKS (HEAT AND FIRE)**



PERFORMANCE LEVELS (X = NOT TESTED)

X	2	X	X	X	X
0-4	0-4	0-4	0-4	0-4	0-4

Resistance to large quantities of molten metal

Small splashes of molten metal

Radiant heat resistant

Convective heat resistance

Contact heat resistance

Limited flame spread

EN ISO 374-1 **CHEMICAL RISKS**



TYPE B

K: Sodium hydroxide 40%

P: Hydrogen peroxide 30%

T: Formaldehyde 37%



FOOD CONTACT

French decree of 05/08/2020

PRODUCT DETAILS

Interior finish	Textile support
Exterior finish	Reinforced grip
Material	Natural latex
Cuff characteristic	Feston Cuff
Colour.s	Blue
Length (cm)	32
Thickness (mm)	1.35
European sizes	6 7 8 9 10

LOGISTIC DETAILS

Packaging	1 pair/bag 5 pairs/bag 50 pairs/carton
-----------	--

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/05/22/1017 EXT 02/06/22
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France