

Heavy-duty neoprene gloves, delivering all-round mechanical and chemical resistance (Length: 450mm/17.7")

- **Advanced defenses:** AlphaTec® 09-928 heavy-duty chemical gloves offer optimal defense against chemical hazards, such as oils, acids, caustics, alcohols and solvents
- **Reinforced protection:** These 450mm-long black hand protection gloves also feature increased puncture and snag resistance, protecting hands and elbows from mechanical hazards
- **Improved ergonomics:** In addition, AlphaTec® 09-928 neoprene work gloves' anatomical design reduces exertion and hand fatigue, resulting in improved comfort, safety and dexterity

Industries

- Metal fabrication
- Chemical

Applications

- Foundry operations
- Handling materials with sharp or rough edges
- Extruding, bending and punching shapes
- Processing sheets, coils, tubes
- Fabricating metal parts, glass sheets
- Unexpected leakages spills or other releases



Previously known as: Scorpio™ 09-928

Key Features

- **Smooth finish neoprene coating:** Broad-spectrum chemical protection
- **Cotton jersey liner:** Increased puncture and snag resistance
- **Anatomical shape:** Improved comfort and reduced hand fatigue assured

Vulcanization Chemical Accelerators

- Zinc Dibutyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 09-928	Liner Material: Cotton Jersey Coating Material: Neoprene	10	450 / 17.7	Black	• 12 pairs in a bag; 3 bags in a carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.