

Bit fine-tooth mini ratchet 1/4"

418B



Product no. 11133030
GTIN 4018754291373
Model 418B




Label.

1/4 Bit fine-tooth mini ratchet RSW.4.5° L.90mm

Properties.

- short version
- reversible
- 80 teeth
- with steel handle
- internal 1/4" hex drive with collar-thrust spring
- for 1/4" screwdriver bits
- for working in tight spaces, with a working angle of just 4.5°
- FOD-preventive due to screwless design
- DIN 3126 / ISO 1173 Form D 6.3



Technologies and features.



Foreign Object Damage


STAHLWILLE protects against FOD (Foreign Object Damage). Our tool is ideal for safety-relevant sectors such as aviation, thanks to the screwless design.



Fine-tooth ratchet mechanism

Our fine-tooth ratchets with 80 teeth re-engage after just 4.5° for maximum precision in confined spaces. 8 pairs of parallel teeth simultaneously ensure maximum load-bearing capacity and particularly smooth running, even at high torques.

Technical drawing.



Technical attributes.

a	11 mm
Inner hex drive (inch)	1/4
Working angle	4.5 °
Width mm (b)	22,5 mm
DIN	DIN 3126 / ISO 1173 Form D 6,3
Length mm (L)	90 mm

Logistics data.

Depth mm (IFS)	90
Width mm (IFS)	23
Height mm (IFS)	10
WEEE/ElektroG	nicht ear-pflichtig
Length (packaged, mm)	140
Width (packaged, mm)	110
Height (packaging, mm)	10
Volume (packaged, dm3)	0.154 dm3
Product no.	11133030
Weight (gross, kg)	0,075
Weight PAP (kg)	0,000
Weight PVC (kg)	0,028
GTIN	4018754291373
Country of origin AWR	GERMANY
Region of origin	Nordrhein-Westfalen
Customs tariff no.	82042000
Packing standard	1
Weight (g)	70 g

Variants.

Product no.	Model No. (ERP)	Description	GTIN
11133030	418B	1/4 Bit fine-tooth mini ratchet RSW.4.5° L.90mm	4018754291373

GTIN.



Accessories (for).



08160027
Screwdriver socket



08310003
Screwdriver bit



08130040
Screwdriver bit



28011010
Socket bit



08340020
Screwdriver bit



08260003
Screwdriver bit



08070123
Screwdriver bit



08160030
Screwdriver socket



08130045
Screwdriver bit



28011013
Socket bit



08340025
Screwdriver bit



08260004
Screwdriver bit



08070124
Screwdriver bit



08160040
Screwdriver socket



08131025
Screwdriver bit



08330003
Screwdriver bit



08340027
Screwdriver bit



08260005
Screwdriver bit



08070125
Screwdriver bit



08010000
Screwdriver bit



08330004
Screwdriver bit



08340030
Screwdriver bit



08260006
Screwdriver bit



08070126
Screwdriver bit



08010001
Screwdriver bit



08330005
Screwdriver bit



08340040
Screwdriver bit



08260008
Screwdriver bit



08070130
Screwdriver bit



08260000
Screwdriver bit



08010002
Screwdriver bit



08330006
Screwdriver bit



08260010
Screwdriver bit



08070127
Screwdriver bit



08010003
Screwdriver bit



08330008
Screwdriver bit



08260016
Screwdriver bit



08070128
Screwdriver bit



08050001
Screwdriver bit



08162010
Screwdriver bit



08090002
Screwdriver bit



08260020
Screwdriver bit



08070129
Screwdriver bit



08250000
Screwdriver bit



08050002
Screwdriver bit



08162015
Screwdriver bit



08090003
Screwdriver bit



08130006
Screwdriver bit



08260024
Screwdriver bit



08300635
Screwdriver bit



08250001
Screwdriver bit



08050003
Screwdriver bit



08162020
Screwdriver bit



08090004
Screwdriver bit



08130007
Screwdriver bit



08161010
5-star screwdriver bit



08300840
Screwdriver bit



08250002
Screwdriver bit



08320001
Screwdriver bit



08162025
Screwdriver bit



08090005
Screwdriver bit



08130008
Screwdriver bit



08161015
5-star screwdriver bit



08301055
Screwdriver bit



08250003
Screwdriver bit



08320002
Screwdriver bit



08162027
Screwdriver bit



08090006
Screwdriver bit



08130009
Screwdriver bit



08161020
5-star screwdriver bit



08301265
Screwdriver bit



08250004
Screwdriver bit



08320003
Screwdriver bit



08162030
Screwdriver bit



08090008
Screwdriver bit



08130010
Screwdriver bit



08161025
5-star screwdriver bit



08301680
Screwdriver bit



08250005
Screwdriver bit



08162040
Screwdriver bit



08200004
Screwdriver bit



08130015
Screwdriver bit



08161027
5-star screwdriver bit



08250006
Screwdriver bit



08160010
Screwdriver socket



08200010
Screwdriver bit



08130020
Screwdriver bit



08161030
5-star screwdriver bit



08230001
Special socket bit



08160015
Screwdriver socket



08200011
Screwdriver bit



08130025
Screwdriver bit



08161040
5-star screwdriver bit



08070120
Screwdriver bit



08160020
Screwdriver socket



08310001
Screwdriver bit



08130027
Screwdriver bit



28011007
Socket bit



08340010
Screwdriver bit



08260001
Screwdriver bit



08070121
Screwdriver bit



08160025
Screwdriver socket



08310002
Screwdriver bit



08130030
Screwdriver bit



28011008
Socket bit



08340015
Screwdriver bit



08260002
Screwdriver bit



08070122
Screwdriver bit



STAHLWILLE Eduard Wille GmbH

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0

info@stahlwille.de · www.stahlwille.com

© STAHLWILLE Eduard Wille GmbH, Wuppertal