

THE BT DECT PORTFOLIO



BT BT1500

Colour: Black



Caller display

50 Number calls list

20 Number redial list

Directory: 50 Name & number

GAP compatible:	yes	Handsfree:	no		
Max. number of handsets:	5	Headset socket:	no		
Max. number of bases:	4	Auto answer:	yes		
Conference call:	yes	Secrecy:	yes	Call waiting indicator:	no
Call transfer:	yes	Handset naming:	no	PBX access code:	no
Internal calls:	yes	Keypad lock:	yes	Repeater compatible:	no
Music on hold:	yes	Power on/off:	yes	Wall mount:	no
Indoor range* (Metres):	50	Inductive coupler:	no		
Outdoor range* (Metres):	300	Earpiece volume control:	yes	Talktime (hours):	12
		Handsfree volume control:	no	Standby (hours):	120
Display type:	mono	Call timer:	yes	Battery type:	NiMH
Display - number of lines #:	2	Clock:	yes	Battery size:	AAA
Backlit:	yes	Alarm:	yes	Battery capacity (mAh):	500
Contrast control:	no	Calendar:	no	Base PSU item code:	066773
		Appointments:	no	Charger PSU item code:	066773
		Illuminated keypad:	no		
		Keypad confirmation tone:	yes	Recording machine	
Handset polyphonic ringtones:	0	Low battery indicator:	yes	Recording time (mins):	up to 20
Handset standard ringtones:	5	Low battery alert:	yes	Playback:	handset & base
Handset ringer on/off:	yes	Out of range indicator:	yes	Outgoing messages:	1
Handset ringer volume control:	yes	Out of range alert:	yes	Recordable outgoing messages:	yes
Visual ring indicator:	no	Handset settings PIN protected:	yes	Answer delay:	yes
Associated ring tone:	no	Belt clip:	no	Time saver:	yes
Base ringtones:	5			Remote access:	yes
Base ringer on/off:	yes			Message advice:	indicator
Base ringer volume control:	yes			Call screening:	yes
		Base settings PIN protected:	yes	Memo:	yes
		Find key on base:	yes	Audable message alert:	yes
SIM card:	no	Keypad on base:	yes		
Caller groups:	no				

Notes:

* In ideal conditions

Including icons and soft keys, as appropriate

Technical support: Is available from the BT Helpdesk on Freephone 0800 218 2182 or via the email link on the product page at www.bt.com/producthelp

Status: Development

THE BT DECT PORTFOLIO



BT BT1500

Weights and dimensions

Base (gms): 176
Handset (gms): 101
Charger (gms): 58

Base (cm): 65 x 138 x 100
Handset (cm): 163 x 53.2 x 31.7
Charger (cm): 51 x 94.8 x 84.3

Giftbox - dimensions/complete/empty

1 Pack: 210 x 180 x 70 (cms) / 542 (gms) / 102 (gms)
2 Pack: 210 x 180 x 85 (cms) / 8580 (gms) / 116 (gms)
3 Pack: 210 x 180 x 120 (cms) / 1182 (gms) / 149 (gms)
4 Pack: 210 x 180 x 145 (cms) / 1470 (gms) / 171 (gms)
Additional handset not available

Overpack - dimensions/complete

1 Pack: 200 x 440 x 228 (cms) / 0 (gms)
2 Pack: 200 x 440 x 275 (cms) / 0 (gms)
3 Pack: 200 x 440 x 255 (cms) / 0 (gms)
4 Pack: 200 x 440 x 305 (cms) / 0 (gms)
Additional handset not available

No. of giftboxes per overpack

1 Pack: 6
2 Pack: 6
3 Pack: 4
4 Pack: 4
Additional handset not available

Pallet Ti's x Hi's

1 Pack: 10 x 5
2 Pack: 9 x 5
3 Pack: 9 x 5
4 Pack: 8 x 5
Additional handset not available

Item code

1 Pack: 066856
2 Pack: 066857
3 Pack: 066858
4 Pack: 066859
Additional handset not available

CSS code

1 Pack not available
2 Pack not available
3 Pack not available
4 Pack not available
Additional handset not available

Barcode

1 Pack: 5016351615324
2 Pack: 5016351615331
3 Pack: 5016351615348
4 Pack: 5016351615355
Additional handset not available

Overpack barcode

1 Pack: 05016351821497
2 Pack: 05016351821503
3 Pack: 05016351821510
4 Pack: 05016351821527
Additional handset not available

Country of manufacture: China