




KRDIN 10-4

Cable Lug KRDIN, 10mm2, M4



Product Properties:

|                                |                   |
|--------------------------------|-------------------|
| Suitable for Class 2 conductor | Yes               |
| Suitable for Class 5 conductor | Yes               |
| Insulated                      | No                |
| Number of mounting holes       | 1 .               |
| Flange shape                   | Ring shape        |
| Colour insulation              | Other             |
| Slender flange model           | No                |
| With sight-hole                | No                |
| Conductor category             | Several           |
| Surface protection             | Tinned            |
| Material                       | Copper            |
| Connecting angle               | 180° (horizontal) |

Dimensions:

|     |        |
|-----|--------|
| HS  | 4.3 mm |
| ID  | 4.5 mm |
| OD  | 6 mm   |
| T   | 1.4 mm |
| P1  | 7 mm   |
| P2  | 8 mm   |
| N   | 10 mm  |
| W   | 9 mm   |
| MOQ | 100 .  |

|                         |                    |
|-------------------------|--------------------|
| Unit                    | pcs                |
| Bolt dimension (metric) | 4 .                |
| Nominal cross section   | 10 mm <sup>2</sup> |

**Approvals:**

|                            |     |
|----------------------------|-----|
| Approved according to CE   | Yes |
| Approved according to UKCA | Ja  |

**Compliance:**

|                   |                               |
|-------------------|-------------------------------|
| Conflict Minerals | Contain "Tin"                 |
| Extended Minerals | Contain "Copper"              |
| PFAS              | No PFAS                       |
| REACH             | No SVHC (Latest. 05 Nov 2025) |
| RoHS              | RoHS 3 (2015/863)             |
| SCIP              | Not Applicable                |
| ECCN (EU)         | No CLASS                      |
| ECCN (US)         | EAR99                         |

**Other information:**

|                    |                                                 |
|--------------------|-------------------------------------------------|
| ETIM-Class         | EC001051 - Tube cable lug for copper conductors |
| ETIM-Release       | 9.0                                             |
| Trademark          | NEMIQ                                           |
| Product Group      | Cable lugs                                      |
| Search Description | SKH2023ERIK2, NYB04                             |
| Alternative SKU    | KRDIN10-4                                       |

**Logistic information:**

|                   |                                                                      |
|-------------------|----------------------------------------------------------------------|
| Barcode           | 733117641254                                                         |
| Country of origin | CN                                                                   |
| Item status       | Stock item, normally in stock with reservation for in between sales. |
| MOQ               | 100 .                                                                |
| Stock code        | KRDIN 10-4                                                           |
| Taric code        | 85369010                                                             |
| Unit              | pcs                                                                  |

\*We reserve the right to make technical changes and disclaim any typographical errors.