

Products Categories

- Part No. index
- Cutters & Pliers
- Wire strippers
- Crimpers
- Tweezers
- Screwdrivers & Wrenches
- Metal working
- Parts cases
- Tool cases
- Tool kits
- Soldering irons & Solder
- Parts & Solder removal equipment
- Measuring instruments
- Optical equipment
- Antistatic products
- Clean products
- Maintenance & Safety products

Tweezers > Precision stainless type

Precision tweezers



Part no.	A	B	C	Tip width	Material	Weight g
	mm					
P-670	120				Stainless	13
P-671	110	10	6	0.2		12
P-672	115					14



P-670 FULLY NON MAGNETIC TWEEZERS

P-671 FULLY NON MAGNETIC TWEEZERS


P-672 FULLY NON MAGNETIC TWEEZERS



Precision tweezers



Part no.	A	B	C	Tip width	Material	Weight g
	mm					
P-653	70	7	6	0.2	Stainless	7
P-654	90	7.5				10
P-655	120					14
P-656	110	10	8		13	
P-657	120				14	



P-653 TWEEZERS

P-654 TWEEZERS

P-844 TWEEZERS HOLDER



P-655 FULLY NON MAGNETIC TWEEZERS

P-656 FULLY NON MAGNETIC TWEEZERS

P-657 FULLY NON MAGNETIC TWEEZERS



Tweezers



Part no.	A	B	C	Tip width	Material	Weight g
	mm					
P-660	120	10	10	0.2	Stainless	14
P-661	110	10	9			
P-662	115		10			
P-664	140	8				13



P-660

TWEEZERS

P-661

TWEEZERS

P-662

TWEEZERS HOLDER



P-664

TWEEZERS



Precision tweezers



Part no.	A	B	C	Tip width	Material	Weight g
	mm					
P-841	110	10	8	0.3	Stainless	13
P-842	120					
P-846	140	9	6			14



P-841

TWEEZERS

P-842

TWEEZERS

P-846

TWEEZERS





COMPLETE
NON-
MAGNETIC

Remains non-magnetized and unaffected by magnetic forces even when working in strong magnetic fields. Ideal when working on precision instruments which are susceptible to even weak magnetism.TIC

NON-
MAGNETIC

May become somewhat magnetized when subjected to a magnetic field, but is non-magnetized in normal environments.

NON-
MAGNETIC

Knob load
When load is applied to the center area and tip is closed

[Home](#)

[Products Categories](#)

[What's New](#)

[Digital Catalog](#)

[About Us](#)

[Contact Us](#)

[Hozan Initiatives](#)

[Global Sales Contacts](#)

Copyright (C) 2016 HOZAN TOOL IND.CO.,LTD. All Rights Reserved.