

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
ES	00		—	SEE SHEET 1	—	—	—

0.96	32.5	30.6	28.5	20	7-292207-0	2-292207-0
0.91	31.0	29.1	27.0	19	6-292207-9	1-292207-9
0.87	29.5	27.6	25.5	18	6-292207-8	1-292207-8
0.82	28.0	26.1	24.0	17	6-292207-7	1-292207-7
0.78	26.5	24.6	22.5	16	6-292207-6	1-292207-6
0.73	25.0	23.1	21.0	15	6-292207-5	1-292207-5
0.69	23.5	21.6	19.5	14	6-292207-4	1-292207-4
0.64	22.0	20.1	18.0	13	6-292207-3	1-292207-3
0.60	20.5	18.6	16.5	12	6-292207-2	1-292207-2
0.55	19.0	17.1	15.0	11	6-292207-1	1-292207-1
0.51	17.5	15.6	13.5	10	6-292207-0	1-292207-0
0.46	16.0	14.1	12.0	9	5-292207-9	292207-9
0.42	14.5	12.6	10.5	8	5-292207-8	292207-8
0.37	13.0	11.1	9.0	7	5-292207-7	292207-7
0.33	11.5	9.6	7.5	6	5-292207-6	292207-6
0.28	10.0	8.1	6.0	5	5-292207-5	292207-5
0.24	8.5	6.6	4.5	4	5-292207-4	292207-4
0.19	7.0	5.1	3.0	3	5-292207-3	292207-3
0.16	5.5	3.6	1.5	2	5-292207-2	292207-2
WEIGHT (g)	C	B	A	Pos.	BLUE	GRAY
	DIMENSIONS				P/N	


RELEASED FOR PUBLICATION

THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

BY TYCO ELECTRONICS CORPORATION.

©

DIMENSIONS:		DWN	MATERIAL		FINISH	
MM		CHK				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	tyco Tyco Electronics Corporation			
0 PLC ± —		PRODUCT SPEC	Electronics SHANGHAI, CHINA			
1 PLC ± SEE SHEET		APPLICATION SPEC	NAME AMP Mini CT Connector 1.5mm Pitch			
2 PLC ± 1 OF 2		WEIGHT	Single Row Post HDR Ass'y (V) DIP Staggered Type with Boss with Kink			
3 PLC ± —			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
4 PLC ± —			A4	00779	C-292207	—
ANGLES ± —						
		CUSTOMER DRAWING		SCALE	SHEET	REV
				NON	2 OF 2	A