

BANDIDO

bolle
SAFETY

An economical model for authentic protection. Made entirely of highly resistant, polycarbonate, Bandido eye shields have inbuilt side protection and allow an excellent panoramic view, thereby guaranteeing a very pleasing price/quality ratio, with an anti-scratch and anti-fog coating.



BANC1



BANESP

Supplied with adjustable cord



BANPSJ



BANPSF




BANWPCC5
without cord



BANXSCI
without cord

Coatings anti-scratch, anti-fog,
anti-static (according to versions)



Europe Bolle Safety
95 Rue Louis Guérin
69100 Villeurbanne - France
tel: 00 33 (0) 4 78 85 23 64
fax: 00 33 (0) 4 78 85 28 56
contact@bolle-safety.com

U.K. Bolle Safety
Unit C83 - Barwell Business Park
Leatherhead Road - Chessington
Surrey - KT9 2NY
tel. 00 44 (0)208 391 4700
fax 00 44 (0)208 391 4733
e-mail : sales@bolle-safety.co.uk


Products ref.	LENSES														FRAMES												
	Risks relating to radiations			Bolle Protection logo	Optical quality			Mechanical Risks				Electrical Risks	Thermal Risks	Coatings (Optional marking K: anti-scratch N: anti-fog)		CE logo	Bolle Protection logo	Standards	Chemical Risks			Electrical Risks	Mechanical Risks			Thermal Risks	CE logo
	EN 169 - welding radiation	EN 170 - UV	EN 172 - Solar (100% UV)		Permanent wear	Intermittent wear	Short period	Low energy impact 45 m/s	Medium energy impact 120 m/s	High energy impact 190 m/s	Extremes of temperature impact	Electric arc short circuiting	Molten metals and hot solids	anti-scratch	anti-fog				Liquid drops	Large dust particles > 5 microns	Gas and fine dust particles < 5 microns	Electric arc short circuiting	Low energy impact 45 m/s	Medium energy impact 120 m/s	High energy impact 190 m/s	Extremes of temperature impact	
BANCI		2-1,2			1		F	N/A	N/A		N/A	N/A					EN 166	N/A	N/A	N/A	N/A	F	N/A	N/A		N/A	
BANESP			5-1,4		1		F	N/A	N/A		N/A	N/A					EN 166	N/A	N/A	N/A	N/A	F	N/A	N/A		N/A	
BANPSJ			5-1,4		1		F	N/A	N/A		N/A	N/A					EN 166	N/A	N/A	N/A	N/A	F	N/A	N/A		N/A	
BANPSF			5-2,5		1		F	N/A	N/A		N/A	N/A					EN 166	N/A	N/A	N/A	N/A	F	N/A	N/A		N/A	
BANWPCC5	5				1		F	N/A	N/A		N/A	N/A					EN 166	N/A	N/A	N/A		F	N/A	N/A		N/A	
BANXSCI					1		F	N/A	N/A		N/A	N/A					EN 166	N/A	N/A	N/A	N/A	F	N/A	N/A		N/A	

N/A: Non applicable

BANCI



BANESP



BANPSJ



BANPSF



BANWPCC5



BANXSCI

CHARACTERISTICS :

Lenses	PC - 2,6 mm - Curve 9,25
Frame	PC
Temples	PC
Strap	Non applicable
Foam	Non applicable
Spare lenses	No

PACKAGING AND EAN 13 CODE :

	BANCI	BANESP	BANPSJ	BANPSF	BANWPCC5
individual plastic bag	3660740002831	3660740003609	3660740003623	3660740003616	3660740003395
10 safety spectacles per box	3660740102838	3660740103606	3660740103620	3660740103613	3660740103392
240 safety spectacles per outer pack	3660740202835	3660740203603	3660740203627	3660740203610	3660740203399

PACKAGING AND EAN 13 CODE :

	BANXSCI
individual plastic bag	3660740000066
10 safety spectacles per box	3660740100063
300 safety spectacles per outer pack	3660740200060

Notified laboratories for certification :

