


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **50-57-9008**  
**Status:** **Active**  
**Overview:** SL™ Modular Connectors  
**Description:** SL™ Crimp Housing, Single Row, Version A, Non-polarized, 8 Circuits

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-71851 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Test Summary TS-70058-001 (PDF)</a>
<a href="#">Product Specification PS-70058 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-70400 (PDF)</a>	



**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	Crimp Housings
Series	<u>70066</u>
Application	Signal, Wire-to-Board
Comments	Version A
Overview	<u>SL™ Modular Connectors</u>
Product Name	SL™
UPC	800753629639

**Physical**

Circuits (maximum)	8
Color - Resin	Black
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	No
Material - Resin	Polyester Alloy
Net Weight	0.057/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Stackable	Yes
Temperature Range - Operating	-40°C to +105°C

**Electrical**


Current - Maximum per Contact	3A
-------------------------------	----

**Material Info**

Old Part Number	70066-0007
-----------------	------------

**Reference - Drawing Numbers**

Product Specification	PS-70058, PS-70400, PS-71851
Sales Drawing	SD-70066-0001-0024
Test Summary	TS-70058-001

<b>EU RoHS</b> <b>ELV and RoHS</b> <b>Compliant</b> <b>REACH SVHC</b> <b>Contains SVHC: No</b> <b>Low-Halogen Status</b> <b>Not Low-Halogen</b>	<b>China RoHS</b> 
---	--

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

70066Series

**Mates With**

[42375](#) , [42377](#) , [70280](#) , [70287](#) , [71308](#) , [70543](#) , [70553](#)

**Use With**

SL™ Crimp Terminal [70058](#) , [71851](#)