

TECHNICAL SPECIFICATION



Flexinet® Mask FFP3 Valved (832)

Box of 5 / BER130-001-M00



DESCRIPTION

The Flexinet™ disposable mask has an ergonomic 3D design to fit most face shapes, with extremely low breathing resistance and mesh outer shell to help the mask retain its shape.

- High efficiency (99% minimum) filtering.

OPTIONS

Box of 5 (BER130-001-M00)

SAFETY STANDARDS

EN 149



JSP Limited, Worsham Mill, Minster Lovell, Oxford OX29 0TA, England.

Tel: +44 (0)1993 826050 / Fax: +44 (0)1993 824411 / Email: sales@jsp-safety.com / Web: www.jsp-safety.com

Do Not Publish without written permission from JSP Limited. Contact copyright@jsp-safety.com. Information correct in the United Kingdom at date of issue and may be subject to change. Any third-party machine and automated translations processed by users may have inaccuracies and should not be relied upon.

Page 1 of 2 / Issued 26 Mar 2025 / Copyright 2018 - 2025. JSP Limited. All Rights Reserved.



SPECIFICATIONS

Classification
FFP3 (Filtering Facepiece Particulate)

Usage
NR (Non-Reusable)



Activated Carbon Layer
No

Maximum Total Inward Leakage (TIL)
2%

UK Assigned Protection Factor
20



Exhalation Valve
Advanced Valve



Nose Bridge
Moulded

Metal Free
Yes

Filter Shelf Life
5 Years



Product Weight
26g



Filter Type
P (Protects Against Solid and Liquid Aerosol)



(D) Resistance to dust clogging
Yes – D marking = passes optional clogging test

Minimum Filtration Efficiency
99% For FFP3 Rated

Nominal Protection Factor
50

Mask Design
Mesh Outer Shell



4 Point Harness adjustment system
Yes


Latex free
No

Mask Material
Polypropylene



BSI Kitemark
Yes

FEATURES



Comfort

A 360° comfort foam area around the inside of the mask provides a perfect fit.



Advanced Valve

Advanced design valve allows for lower breathing resistance.



Protective Grill

Flexible cover to protect and retain the shape of the mask and protect the wearer against possible damage to the filter.

RANGE



DOWNLOADS



[Image Pack \(ZIP\)](#)



[doc-olympus-800-series-832.pdf \(PDF\)](#)



JSP Limited, Worsham Mill, Minster Lovell, Oxford OX29 0TA, England.

Tel: +44 (0)1993 826050 / Fax: +44 (0)1993 824411 / Email: sales@jspsafety.com / Web: www.jspsafety.com

Do Not Publish without written permission from JSP Limited. Contact copyright@jspsafety.com. Information correct in the United Kingdom at date of issue and may be subject to change. Any third-party machine and automated translations processed by users may have inaccuracies and should not be relied upon.

Page 2 of 2 / Issued 26 Mar 2025 / Copyright 2018 - 2025. JSP Limited. All Rights Reserved.

