

Thick natural latex rubber gloves, granting superior protection for heavy-duty applications

- **Advanced defenses:** With 0.73mm/29 mil thickness, AlphaTec® 87-950 black protective gloves are 50% thicker than standard flock-lined gloves, for greater durability and superb mechanical and chemical resistance*
- **Increased comfort:** Thanks to their pure cotton flock lining, AlphaTec® 87-950 hand protection gloves also absorb perspiration, keeping hands dry and comfortable with sustained wear
- **Enhanced cleanliness:** These chemical-resistant gloves also undergo an external chlorination treatment, for added cleanliness
- **Assured quality:** In addition, they boast an AQL of 1.5

**protects against ketones, salts, detergents, alcohols, alkalis and fats*

Industries

- Construction
- Machinery and Equipment
- Infrastructure Maintenance
- Chemical

Applications

- Maintenance of plant and heavy equipment
- Chemical processing and preparation
- Janitorial use



Previously known as: Extra 87-950

Key Features

- **Thick natural rubber latex:** Superb mechanical and chemical protection*
- **100% cotton flock lining:** For safety gloves offering drier comfort
- **External chlorination treatment:** Harder surface, added cleanliness

*protects against ketones, salts, detergents, alcohols, alkalis and fats

Vulcanization Chemical Accelerators

- Natural rubber proteins
- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 87-950	Coating Material: Natural Rubber Latex	7.5, 8, 9, 10, 11	325 / 12.8	Black	• 12 pairs per bag, 12 bags per carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.