TECHNICAL DATASHEET
SPORTS SAFETY TRAINER

HECKEL
PERFORMANCE WITH STYLE

SNEAK-R SILVER LOW

PRODUCT CODE	SIZES	WIDTH	WEIGHT*
78013	35 > 52	11	570 g

i-PUREnrj planet clima zone ESD 100 % metal free

Made in Italy

EN 20345:2022 + A1:2024

S1 PS **FO** **SR**

AREAS OF APPLICATION







COMPOSITION

OUTSOLE	PU i-PUREnrj planet
UPPER	techmesh rear Active Stability TPU reinforcement front TPU film
CLOSING SYSTEM	laces with eyelets
LINING	distance-mesh
TONGUE	breathable textile and mesh with gussets
TOE CAP	non-metallic composite
PERFORATION-RESISTANT MIDSOLE	non-metallic textile
INSOLE	top in non-woven textile bottom in porous PU memory foam forefoot and heel shock absorbers

OPTIONS

MULTIPLE FIT SYSTEM	available in widths 10 and 12 by replacing the insole

climazone breathability



KEY FEATURES

- HIGH-PERFORMANCE CUSHIONING AND ENERGY RETURN WITH I-PURENRJ PLANET
- ACTIVE STABILITY SUPPORT STRUCTURE FOR ENHANCED STABILITY
- LIGHTWEIGHT MATERIALS AND REDUCED ADHESIVES (CLIMAZONE) FOR BREATHABILITY
- PROTECTION AGAINST FINE PERFORATION RISKS UP TO 3.0 MM (PS)
- WIDE RANGE OF SIZES, WIDTHS AND WOMEN'S LAST 35 > 40

*per foot in size 42

UVEX HECKEL s.a.s. • 44 Rue d'Engwiller - La Walck, 67350 Val-De-Moder (France) • **Tel.** +33 (0)3 88 07 61 08
France email contact.france@uvex-heckel.fr • **Export email** contact.export@uvex-heckel.fr • **www.heckel.fr**

TECHNICAL DATASHEET
SPORTS SAFETY TRAINER

HECKEL
PERFORMANCE WITH STYLE

PACKAGING

SALES UNIT	1 pair
QUANTITY PER CARTON	10 pairs

ACCESSORIES

INSOLE WIDTH 10	67962
INSOLE WIDTH 11	67963
INSOLE WIDTH 12	67964

ADDITIONAL REQUIREMENTS

Oil-resistant outsole **FO**

Slip resistance (ceramic tile floor + glycerine) **SR**

SUSTAINABILITY

PRODUCT

FREE FROM HARMFUL SUBSTANCES PER **UVEX LIST, EXCEEDING REACH REQUIREMENTS**

7 % RECYCLED MATERIALS
ACCORDING WITH ISO 14021

COMPOSITION

OUTSOLE	15% recycled PU granules from production waste
PERFORATION-RESISTANT MIDSOLE	21% recycled polyester

PACKAGING

SHOE BOX MADE FROM
90% RECYCLED MATERIALS

INSTRUCTIONS FOR USE MADE FROM
100% RECYCLED MATERIALS

CARBON FOOTPRINT

7.66 KG CO_2E CRADLE-TO-CUSTOMER
9.21 KG CO_2E CRADLE-TO-GRAVE
CALCULATION DATE: 07/2026*

PRODUCTION

ISO 14001-CERTIFIED
PRODUCTION SITE IN CEVA (ITALY)

*__Calculation method:__ IPCC 2021 GWP100a, in accordance with ISO 14067 • **Database/Software**: Company-specific calculation based on SimaPro and ecoinvent • **Functional unit**: single product, or a pair where products are used in pairs • **Scope**: Cradle-to-Grave • Unit: kg CO2e • The CO2e values stated apply to the defined calculation period and are subject to change at any time..

CE certified PPE • **Update**: 09/2026 • UVEX HECKEL s.a.s. reserved the right to change product features without notice • photos and documents are non-contractual

UVEX HECKEL s.a.s. • 44 Rue d'Engwiller - La Walck, 67350 Val-De-Moder (France) • **Tel.** +33 (0)3 88 07 61 08
France email contact.france@uvex-heckel.fr • **Export email** contact.export@uvex-heckel.fr • **www.heckel.fr**