

"PanelSeT SF/SM partial 19" swing rack - 355 mm"

Local distributor code: 398255648

NSYRSWP6

EAN Code: 3606480067327

Main

Range	PanelSeT
Accessory / separate part category	Mounting accessory
Product or component type	19" rack
Application	Electronic application
For enclosure nominal dimensions	- H: 355 mm
Rack type	Swing
Mounting location	Front of enclosure
Mounting support	Partial 19" swing rack support
Range compatibility	PanelSeT PanelSeT SF PanelSeT PanelSeT SM
Device composition	1 rack
Number of units 19"	6

Complementary

Rack coverage	Partial	
Material	Steel	
Enclosure/cubicle description	Floor-standing enclosure	
Surface finish	Zinc coated	
Lock type	Lock 5 mm double bar	
fixing mode	By fixing element	
Adjustment	Adjustable in depth every 25 mm	
Permanent permissible load	2 kg per unit	
Opening of the 19" racks	Reversible 120 °	
Height	355 mm	
Width	600 mm 800 mm	
Depth	335 mm	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.500 cm

Package 1 Width	34.500 cm
Package 1 Length	52.000 cm
Package 1 Weight	2.522 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	25
Package 2 Height	50.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	75.000 kg

Logistical informations

Country of origin ES

Contractual warranty

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	18
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances		
Packaging made with recycled cardboard	No	
Packaging without single use plastic	No	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142	
REACh Regulation	REACh Declaration	

Use Again


○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Product datasheet

NSYRSWP6

Technical Illustration

Dimensions



Product datasheet

NSYRSWP6

Image of product / Alternate images

Alternative

