

DM-PTMC-3 - Marker adapter



1162606

<https://www.phoenixcontact.com/gb/products/1162606>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker adapter, for accommodating the marking, depth: 30 mm, width: 22 mm, height: 9 mm, color: gray

Your advantages

- Easy marking options
- Accessories for snapping on to PTMC

Commercial data

Item number	1162606
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BE6ZWX
Product key	BE6ZWX
GTIN	4063151172985
Weight per piece (including packing)	3.54 g
Weight per piece (excluding packing)	3.54 g
Customs tariff number	85389099
Country of origin	PL

DM-PTMC-3 - Marker adapter

1162606

<https://www.phoenixcontact.com/gb/products/1162606>



Technical data

Product properties

Product type	Mounting material
--------------	-------------------

Dimensions

Width	22 mm
Height	9 mm
Depth	30 mm

Material specifications

Color	gray (RAL 7042)
Material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

DM-PTMC-3 - Marker adapter



1162606

<https://www.phoenixcontact.com/gb/products/1162606>

Classifications

ECLASS

ECLASS-12.0	27141190
ECLASS-13.0	27141190

ETIM

ETIM 9.0	EC002848
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

DM-PTMC-3 - Marker adapter

1162606

<https://www.phoenixcontact.com/gb/products/1162606>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk