
Product datasheet

Specifications



Front Plate, PrismaSeT P & G, for FuPact INF63-160A 3P/4P horizontal/vertical fixed, 5M, enclosure W600mm

LVS03309

EAN Code: 3606482452688

Main

Range	PrismaSeT
Range of product	PrismaSeT G PrismaSeT P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	Prisma Prisma G enclosure Prisma Prisma P cubicle
Type of front plate	Cut-out
Installed device	FuPact: fixed INF63 - control: extended rotary handle - vertical installation FuPact: fixed INF63 - control: extended rotary handle - horizontal installation FuPact: fixed INF100...160 - control: extended rotary handle - vertical installation FuPact: fixed INF100...160 - control: extended rotary handle - horizontal installation
Poles description	3 x 3P: mounting plate support: INF63 vertical installation 2 x 4P: mounting plate support: INF63 vertical installation 2 x 3P: mounting plate support: INF100...160 vertical installation 2 x 4P: mounting plate support: INF100...160 vertical installation 1 x 3P: mounting plate support: INF63 horizontal installation 1 x 4P: mounting plate support: INF63 horizontal installation 1 x 3P: mounting plate support: INF100...160 horizontal installation 1 x 4P: mounting plate support: INF100...160 horizontal installation
Operating position	Vertical Horizontal

Complementary

Enclosure/cubicle description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm depth 400 mm
Connection position	Direct connection
Number of vertical modules [50 mm]	5
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA
Material	Steel
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Smooth Matt
Colour	White (RAL 9001)
Width	500 mm
Height	250 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Net weight	1.04 kg
Quantity per set	Set of 1
functional unit	600 mm Prisma G floor-standing enclosure FuPact INF63 fixed extended rotary handle horizontal 3P 1 direct 5 600 mm Prisma G wall-mounted enclosure FuPact INF63 fixed extended rotary handle horizontal 3P 1 direct 5 600 mm Prisma G floor-standing enclosure FuPact INF63 fixed extended rotary handle horizontal 4P 1 direct 5 600 mm Prisma G wall-mounted enclosure FuPact INF63 fixed extended rotary handle horizontal 4P 1 direct 5 600 mm Prisma G floor-standing enclosure FuPact INF63 fixed extended rotary handle vertical 3P 3 direct 5 600 mm Prisma G wall-mounted enclosure FuPact INF63 fixed extended rotary handle vertical 3P 3 direct 5 600 mm Prisma G floor-standing enclosure FuPact INF63 fixed extended rotary handle vertical 4P 2 direct 5 600 mm Prisma G wall-mounted enclosure FuPact INF63 fixed extended rotary handle vertical 4P 2 direct 5 600 mm Prisma G floor-standing enclosure FuPact INF100...160 fixed extended rotary handle horizontal 3P 1 direct 7 600 mm Prisma G wall-mounted enclosure FuPact INF100...160 fixed extended rotary handle horizontal 3P 1 direct 7 600 mm Prisma G floor-standing enclosure FuPact INF100...160 fixed extended rotary handle horizontal 4P 1 direct 7 600 mm Prisma G wall-mounted enclosure FuPact INF100...160 fixed extended rotary handle horizontal 4P 1 direct 7 600 mm 400 mm Prisma G floor-standing enclosure FuPact INF100...160 fixed extended rotary handle vertical 3P 2 direct 7 600 mm 400 mm Prisma G wall-mounted enclosure FuPact INF100...160 fixed extended rotary handle vertical 3P 2 direct 7 600 mm Prisma G floor-standing enclosure FuPact INF100...160 fixed extended rotary handle vertical 4P 2 direct 7 600 mm Prisma G wall-mounted enclosure FuPact INF100...160 fixed extended rotary handle vertical 4P 2 direct 7 650 mm 400 mm Prisma P cubicle FuPact INF63 fixed extended rotary handle horizontal 3P 1 direct 5 650 mm 400 mm Prisma P cubicle FuPact INF63 fixed extended rotary handle horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle FuPact INF63 fixed extended rotary handle vertical 3P 2 direct 5 650 mm 400 mm Prisma P cubicle FuPact INF63 fixed extended rotary handle vertical 4P 2 direct 5 650 mm 400 mm Prisma P cubicle FuPact INF100...160 fixed extended rotary handle horizontal 3P 1 direct 5 650 mm 400 mm Prisma P cubicle FuPact INF100...160 fixed extended rotary handle horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle FuPact INF100...160 fixed extended rotary handle vertical 3P 2 direct 5 650 mm 400 mm Prisma P cubicle FuPact INF100...160 fixed extended rotary handle vertical 4P 2 direct 5

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	30.500 cm
Package 1 Length	51.000 cm
Package 1 Weight	1.094 kg
Unit Type of Package 2	S04
Number of Units in Package 2	9
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	10.745 kg

Unit Type of Package 3	P12
Number of Units in Package 3	36
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	55.000 kg

Logistical informations

Country of origin	FR

Contractual warranty

Warranty (in months)	18

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Environmental footprint

Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant
REACh Regulation	Free of Substances of Very High Concern above the threshold
Halogen-free status	Halogen free plastic parts product
PVC free	Yes
Silicone-free	Yes

Use Longer

Lifetime extension

Repair	No

Use Again

Repack and remanufacture

End of life manual availability	No need of specific recycling operations
Take-back	No