

Features

- Material Tungsten Carbide Tipped
- Integrated safety collar
- Machined from a single piece of steel
- Pilot drill with spring for automatic plug removal
- Variable tip placement

RS PRO Shallow Cut TCT Holesaws, Tungsten Carbide Tipped



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Shallow Cut Tungsten Carbide Tipped Holesaws

RS PRO Tungsten Carbide Tipped Shallow cut Holesaw has a Tungsten Carbide tip for a long edge life and increased heat resistance, with the teeth angled for optimal performance and variable tip placement for reduced vibration.

The Holesaw is manufactured from a single piece of steel to provide extra strength and durability, complete with an integrated safety collar to prevent over-cutting. The pilot drill is replaceable and has a built-in spring for automatic plug removal. Suitable for cutting stainless steel, carbon steel, aluminium and cast iron, up to a thickness of 4.5mm.

General Specifications

Diameter	See details below
Drill Bit Type	Core Drill Bit
Arbor Included	Yes
Material	Tungsten Carbide Tipped
Cut Depth	See details below
Bimetal	No
Number of Pieces	1
Shank Diameter	See details below
Type	Hole Saw

Stock No.	Product Name	Diameter	Cut Depth	Shank Diameter
XXX-XXXX 0827567	TCT Shallow Cut Holesaw	14mm	4.5mm	10mm
XXX-XXXX 0827569	TCT Shallow Cut Holesaw	16mm	4.5mm	10mm
XXX-XXXX 0827570	TCT Shallow Cut Holesaw	17mm	4.5mm	10mm
XXX-XXXX 0827571	TCT Shallow Cut Holesaw	19mm	4.5mm	10mm
XXX-XXXX 0827572	TCT Shallow Cut Holesaw	20mm	4.5mm	10mm
XXX-XXXX 0827573	TCT Shallow Cut Holesaw	21mm	4.5mm	10mm
XXX-XXXX 0827575	TCT Shallow Cut Holesaw	22mm	4.5mm	10mm
XXX-XXXX 0827576	TCT Shallow Cut Holesaw	24mm	4.5mm	10mm
Stock No.	Product Name	Diameter	Cut Depth	Shank Diameter

XXX-XXXX 0827577	TCT Shallow Cut Holesaw	25mm	4.5mm	10mm
XXX-XXXX 0827535	TCT Shallow Cut Holesaw	27mm	4.5mm	10mm
XXX-XXXX 0827536	TCT Shallow Cut Holesaw	29mm	4.5mm	10mm
XXX-XXXX 0827537	TCT Shallow Cut Holesaw	30mm	4.5mm	10mm
XXX-XXXX 0827538	TCT Shallow Cut Holesaw	32mm	4.5mm	10mm
XXX-XXXX 0827539	TCT Shallow Cut Holesaw	33mm	4.5mm	10mm
XXX-XXXX 0827540	TCT Shallow Cut Holesaw	35mm	4.5mm	10mm
XXX-XXXX 0827541	TCT Shallow Cut Holesaw	37mm	4.5mm	10mm
XXX-XXXX 0827542	TCT Shallow Cut Holesaw	38mm	4.5mm	10mm
XXX-XXXX 0827543	TCT Shallow Cut Holesaw	40mm	4.5mm	10mm
XXX-XXXX 0827544	TCT Shallow Cut Holesaw	41mm	4.5mm	10mm
XXX-XXXX 0827545	TCT Shallow Cut Holesaw	43mm	4.5mm	10mm
XXX-XXXX 0827547	TCT Shallow Cut Holesaw	44mm	4.5mm	10mm
XXX-XXXX 0827548	TCT Shallow Cut Holesaw	46mm	4.5mm	10mm
XXX-XXXX 0827549	TCT Shallow Cut Holesaw	48mm	4.5mm	10mm
XXX-XXXX 0827550	TCT Shallow Cut Holesaw	49mm	4.5mm	10mm
XXX-XXXX 0827551	TCT Shallow Cut Holesaw	51mm	4.5mm	10mm
XXX-XXXX 0827553	TCT Shallow Cut Holesaw	52mm	4.5mm	10mm
XXX-XXXX 0827554	TCT Shallow Cut Holesaw	54mm	4.5mm	10mm
XXX-XXXX 0827555	TCT Shallow Cut Holesaw	56mm	4.5mm	10mm
XXX-XXXX 0827556	TCT Shallow Cut Holesaw	57mm	4.5mm	10mm
XXX-XXXX 0827557	TCT Shallow Cut Holesaw	59mm	4.5mm	10mm
XXX-XXXX 0827558	TCT Shallow Cut Holesaw	60mm	4.5mm	10mm
XXX-XXXX 0827559	TCT Shallow Cut Holesaw	62mm	4.5mm	10mm
Stock No.	Product Name	Diameter	Cut Depth	Shank Diameter
XXX-XXXX 0827560	TCT Shallow Cut Holesaw	64mm	4.5mm	10mm
XXX-XXXX 0827561	TCT Shallow Cut Holesaw	65mm	4.5mm	13mm
XXX-XXXX 0827562	TCT Shallow Cut Holesaw	67mm	4.5mm	13mm

XXX-XXXX 0827563	TCT Shallow Cut Holesaw	68mm	4.5mm	13mm
XXX-XXXX 0827564	TCT Shallow Cut Holesaw	70mm	4.5mm	13mm
XXX-XXXX 0827565	TCT Shallow Cut Holesaw	73mm	4.5mm	13mm
XXX-XXXX 0827566	TCT Shallow Cut Holesaw	76mm	4.5mm	13mm

Approvals

Declarations	REACH DoC
--------------	-----------

