



Product data sheet

Power tools for trade & industry

Plunge Saw

PRO GKT 55 GCE



Precision and power for a clean cut

The most important data

Rated input power	1,400 W
Saw blade diameter	165 mm
No-load speed	3,600 – 6,250 rpm

Order number 0 601 675 071

Technical data

Additional data

Rated input power	1400 W
Saw blade diameter	165 mm
Voltage, electrical	230 V
Saw blade bore diameter	20 mm
No-load speed	3,600 – 6,250 rpm
Weight	4.7 kg
Baseplate	310 x 240 mm
Bevel angle	-1 - 47 °
Cable length	3.9 m
Cutting depth without guide rail (90°)	57 mm
Cutting depth without guide rail (45°)	42 mm

Noise/vibration information

Wood sawing

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Adjustable speed setting enables cuts in multitude of materials
- Efficient dust extraction system and noise-reduced blade make work comfortable, especially indoors
- High-quality machine components, precision saw blade, and matching guide rail system ensure extremely precise results

**HEAVY
DUTY**



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/ke/en/wac/>

