



Price\* : 395.47 GBP



## Main

Range	TeSys
Product name	TeSys LE
Device short name	LE4D
Product or component type	Enclosed DOL starter
Device application	Standard
Material	Polycarbonate
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Fuse disconnecter Contactor
[Ie] rated operational current	35 A AC-3
Motor power kW	15 kW at 380/400 V AC 50/60 Hz 15 kW at 415 V AC 50/60 Hz 15 kW at 440 V AC 50/60 Hz 7.5 kW at 220/230 V AC 50/60 Hz 18.5 kW at 500 V AC 50/60 Hz 18.5 kW at 660/690 V AC 50/60 Hz
[Uc] control circuit voltage	400 V AC 50/60 Hz
[Ithe] conventional enclosed thermal current	35 A
Associated fuse rating	32 A 14 x 51 mm aM
Control type	Push-button start green I Push-button stop/reset red O

## Complementary

Cable entry number	2 cable entry : ISO20 top 2 cable entry : ISO20 bottom 2 cable entry : ISO25 top 2 cable entry : ISO25 bottom 2 cable entry : ISO32 top 2 cable entry : ISO40 top
--------------------	--

2 cable entry : ISO32 bottom  
2 cable entry : ISO40 bottom

Width	186 mm
Height	330 mm
Depth	175.5 mm
Product weight	5.19 kg

## Environment

IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0925 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product environmental</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------