

1292331
<https://www.phoenixcontact.com/in/products/1292331>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ex i-Relay module isolates binary Ex i and non Ex i signal and control circuits, and is used for intrinsically safe activation of Ex i field currents via one changeover contact relay per channel.
number of channels: 2, Standard configuration, Loop-powered, 4-way isolation, Safety Integrity Level (SIL, IEC 61508): 2, Screw connection

Commercial data

Item number	1292331
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DK121W
GTIN	4063151525613
Weight per piece (including packing)	189.3 g
Weight per piece (excluding packing)	160 g
Country of origin	DE

MACX MCR-EX-AP-2REL-2DI-LP - Relay module



1292331

<https://www.phoenixcontact.com/in/products/1292331>

Technical data

Notes

Notes on operation	Installation conditions influence the ambient temperature. Please refer to the operating instructions.
--------------------	---

Product properties

Product type	Relay Module
Product family	MACX Analog
No. of channels	2

Electrical properties

Electrical isolation	4-way isolation
----------------------	-----------------

Electrical isolation Input/output IEC/EN 60079-11

Standards/regulations	IEC/EN 60079-11
Rated insulation voltage	375 V _{PP}

Electrical isolation Input 1 / input 2

Test voltage	350 V (50 Hz, 60 s)
--------------	---------------------

Supply

Supply voltage range	loop-powered, no external supply necessary
Power dissipation	≤ 0.4 W

Input data

Control

Description of the input	Control input, not intrinsically safe
Voltage input signal	12 V ... 31.2 V (Switching signal)
Current consumption	< 25 mA (12 V)
	< 17 mA (24 V ... 31.2 V)

Output data

Switching: Relay

Output description	intrinsically safe
Contact switching type	1 changeover contact per channel
Minimum switching voltage	1 V (1 mA)
Maximum switching voltage	45 V DC (0.25 A)
	30 V DC (4 A)
	45 V AC (4 A, cos φ >0.7)
Typical response time	≤ 10 ms
Typical turn-off time	≤ 10 ms
Switching frequency	≤ 15 Hz

Connection data

MACX MCR-EX-AP-2REL-2DI-LP - Relay module



1292331

<https://www.phoenixcontact.com/in/products/1292331>

Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Conductor cross section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 14

Ex data

Ex installation (EPL)	Gc
Ex i circuits (EPL)	Ga
	Da
	Ma

Safety data

Input voltage U_i	45 V AC
Input current I_i	4 A
Max. internal inductance L_i	negligible
Max. internal capacitance C_i	negligible
Safety-related maximum voltage U_m	253 V AC


Safety data

Input voltage U_i	45 V DC
Input current I_i	0.25 A
Max. internal inductance L_i	negligible
Max. internal capacitance C_i	negligible
Safety-related maximum voltage U_m	253 V AC

Safety data

Input voltage U_i	30 V DC
Input current I_i	4 A
Max. internal inductance L_i	negligible
Max. internal capacitance C_i	negligible
Safety-related maximum voltage U_m	253 V AC

Dimensions

Dimensional drawing	
Width	17.5 mm
Height	112.5 mm
Depth	113.7 mm

MACX MCR-EX-AP-2REL-2DI-LP - Relay module



1292331

<https://www.phoenixcontact.com/in/products/1292331>

Depth NS 35/7,5	114.5 mm (Snapped onto DIN rail NS 35/7,5 in accordance with EN 60715)
-----------------	--

Material specifications

Flammability rating according to UL 94	V0
Housing material	PA 6.6

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20 (Terminal blocks) IP30 (Housing)
Ambient temperature (operation)	-20 °C ... 70 °C (Stand-alone device: any mounting position) -20 °C ... 70 °C (Group assembly: vertical DIN rail without circulating air) -20 °C ... 70 °C (Group assembly: vertical DIN rail with circulating air) -20 °C ... 70 °C (Group assembly: horizontal DIN rail without circulating air) -20 °C ... 70 °C (Group assembly: horizontal DIN rail with circulating air)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m
Permissible humidity (operation)	≤ 95 % (non-condensing)

Approvals

ATEX

Identification	⊕ II (1) G [Ex ia Ga] IIC ⊕ II (1) D [Ex ia Da] IIIC ⊕ II 3(1) G Ex ec nC [ia Ga] IIC T4 Gc ⊕ I (M1) [Ex ia Ma] I
----------------	--

IECEX

Identification	[Ex ia Ga] IIC [Ex ia Da] IIIC Ex ec nC [ia Ga] IIC T4 Gc [Ex ia Ma] I
----------------	---

Safety Integrity Level (SIL, IEC 61508)

Identification	2
----------------	---

EMC data

Electromagnetic compatibility	Tested in accordance with the following standards and regulations: EN 61326-1 For industrial use, NAMUR NE 21
-------------------------------	---

Standards and regulations

Electrical isolation	4-way isolation
----------------------	-----------------

MACX MCR-EX-AP-2REL-2DI-LP - Relay module



1292331

<https://www.phoenixcontact.com/in/products/1292331>

Mounting

Mounting type	NS 35/15, NS 35/7,5
Mounting position	vertical, horizontal

MACX MCR-EX-AP-2REL-2DI-LP - Relay module


1292331

<https://www.phoenixcontact.com/in/products/1292331>



Drawings

Dimensional drawing




MACX MCR-EX-AP-2REL-2DI-LP - Relay module



1292331

<https://www.phoenixcontact.com/in/products/1292331>

Block diagram



MACX MCR-EX-AP-2REL-2DI-LP - Relay module



1292331

<https://www.phoenixcontact.com/in/products/1292331>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1292331>

Functional Safety

Approval ID: 22/05-248 R032 V1R0



IECEx

Approval ID: IECEx BVS 21.0058X



ATEX

Approval ID: BVS 21 ATEX E 053X

MACX MCR-EX-AP-2REL-2DI-LP - Relay module



1292331

<https://www.phoenixcontact.com/in/products/1292331>

Classifications

ECLASS

ECLASS-11.0	27210192
ECLASS-12.0	27210192
ECLASS-13.0	27210192

ETIM

ETIM 9.0	EC002498
----------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	527a5898-3267-4b3a-8030-0259c0dda785

MACX MCR-EX-AP-2REL-2DI-LP - Relay module



1292331

<https://www.phoenixcontact.com/in/products/1292331>

Accessories

MCR-DP - Separating plate

1430594

<https://www.phoenixcontact.com/in/products/1430594>



The partition plate is used to maintain Ex i isolating distances when Ex i and non-Ex i devices are mounted side by side on a DIN rail.

ME-TBUS-A MC 1,5-2 - DIN rail bus connectors

1351974

<https://www.phoenixcontact.com/in/products/1351974>



DIN rail connector adapter (2-pos.) for connection of MACX MCR-EX-AP ... devices on the right side to the MACX MCR-PTB(-SP) power module with DIN rail connector ME 17,5 TBUS 1,5/5-ST-3,81 GY for bridging the supply voltage.

MACX MCR-EX-AP-2REL-2DI-LP - Relay module



1292331

<https://www.phoenixcontact.com/in/products/1292331>

ME-TBUS-A IMC1,5-2 - DIN rail bus connectors

1351982

<https://www.phoenixcontact.com/in/products/1351982>



DIN rail connector adapter (2-pos.) for connection of MACX MCR-EX-AP... devices on the left side to the MACX MCR-PTB(-SP) power module with DIN rail connector ME 17,5 TBUS 1,5/5-ST-3,81 GY for bridging the supply voltage.

MPS-IH WH - Insulating sleeve

0201663

<https://www.phoenixcontact.com/in/products/0201663>

Insulating sleeve, color: white



MACX MCR-EX-AP-2REL-2DI-LP - Relay module



1292331

<https://www.phoenixcontact.com/in/products/1292331>

MPS-IH RD - Insulating sleeve

0201676

<https://www.phoenixcontact.com/in/products/0201676>

Insulating sleeve, color: red




MPS-IH BU - Insulating sleeve

0201689

<https://www.phoenixcontact.com/in/products/0201689>

Insulating sleeve, color: blue



MACX MCR-EX-AP-2REL-2DI-LP - Relay module

1292331

<https://www.phoenixcontact.com/in/products/1292331>



MPS-IH YE - Insulating sleeve

0201692

<https://www.phoenixcontact.com/in/products/0201692>

Insulating sleeve, color: yellow



MPS-IH GN - Insulating sleeve

0201702

<https://www.phoenixcontact.com/in/products/0201702>

Insulating sleeve, color: green



MACX MCR-EX-AP-2REL-2DI-LP - Relay module

1292331

<https://www.phoenixcontact.com/in/products/1292331>



MPS-IH GY - Insulating sleeve

0201728

<https://www.phoenixcontact.com/in/products/0201728>

Insulating sleeve, color: gray



MPS-IH BK - Insulating sleeve

0201731

<https://www.phoenixcontact.com/in/products/0201731>

Insulating sleeve, color: black



MACX MCR-EX-AP-2REL-2DI-LP - Relay module



1292331

<https://www.phoenixcontact.com/in/products/1292331>

MPS-MT - Test plug

0201744

<https://www.phoenixcontact.com/in/products/0201744>



Test plug, with solder connection up to 1 mm² conductor cross section, number of positions: 1, color: gray

UC-EMLP (11X9) - Plastic label

0819291

<https://www.phoenixcontact.com/in/products/0819291>



Plastic label, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: adhesive, Number of individual labels: 10, text field height: 9 mm, text field width: 11 mm

MACX MCR-EX-AP-2REL-2DI-LP - Relay module




1292331

<https://www.phoenixcontact.com/in/products/1292331>

UC-EMLP (11X9) YE - Plastic label

0822602

<https://www.phoenixcontact.com/in/products/0822602>



Plastic label, Sheet, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: adhesive, Number of individual labels: 10, text field height: 9 mm, text field width: 11 mm

UC-EMLP (11X9) CUS - Plastic label

0824547

<https://www.phoenixcontact.com/in/products/0824547>



Plastic label, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: adhesive, text field height: 9 mm, text field width: 11 mm

MACX MCR-EX-AP-2REL-2DI-LP - Relay module




1292331

<https://www.phoenixcontact.com/in/products/1292331>

UC-EMLP (11X9) YE CUS - Plastic label

0824548

<https://www.phoenixcontact.com/in/products/0824548>



Plastic label, can be ordered: by sheet, yellow, labeled according to customer specifications, mounting type: adhesive, text field height: 9 mm, text field width: 11 mm

UC-EMLP (11X9) SR - Plastic label

0828094

<https://www.phoenixcontact.com/in/products/0828094>



Plastic label, Sheet, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: adhesive, Number of individual labels: 10, text field height: 9 mm, text field width: 11 mm

MACX MCR-EX-AP-2REL-2DI-LP - Relay module



1292331

<https://www.phoenixcontact.com/in/products/1292331>

UC-EMLP (11X9) SR CUS - Plastic label

0828098

<https://www.phoenixcontact.com/in/products/0828098>



Plastic label, can be ordered: by sheet, silver, labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 10, text field height: 9 mm, text field width: 11 mm

US-EMLP (11X9) - Plastic label

0828789

<https://www.phoenixcontact.com/in/products/0828789>



Plastic label, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, Number of individual labels: 135, text field height: 9 mm, text field width: 11 mm

MACX MCR-EX-AP-2REL-2DI-LP - Relay module



1292331

<https://www.phoenixcontact.com/in/products/1292331>

US-EMLP (11X9) YE - Plastic label

0828871

<https://www.phoenixcontact.com/in/products/0828871>



Plastic label, Card, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, Number of individual labels: 135, text field height: 9 mm, text field width: 11 mm

US-EMLP (11X9) SR - Plastic label

0828872

<https://www.phoenixcontact.com/in/products/0828872>



Plastic label, Card, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, Number of individual labels: 135, text field height: 9 mm, text field width: 11 mm

MACX MCR-EX-AP-2REL-2DI-LP - Relay module



1292331

<https://www.phoenixcontact.com/in/products/1292331>

LS-EMLP (11X9) WH - Device marker

0831678

<https://www.phoenixcontact.com/in/products/0831678>

Device marker, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, mounting type: adhesive, Number of individual labels: 255, text field height: 9 mm, text field width: 11 mm




LS-EMLP (11X9) SR - Device marker

0831705

<https://www.phoenixcontact.com/in/products/0831705>

Device marker, Sheet, silver, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, mounting type: adhesive, Number of individual labels: 255, text field height: 9 mm, text field width: 11 mm



MACX MCR-EX-AP-2REL-2DI-LP - Relay module



1292331

<https://www.phoenixcontact.com/in/products/1292331>

LS-EMLP (11X9) YE - Device marker

0831732

<https://www.phoenixcontact.com/in/products/0831732>

Device marker, Sheet, yellow, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, mounting type: adhesive, Number of individual labels: 255, text field height: 9 mm, text field width: 11 mm



SZS 0,6X3,5 - Screwdriver

1205053

<https://www.phoenixcontact.com/in/products/1205053>

Actuation tool, for ST terminal blocks, insulated, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip



Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in