

Parts List Report

Assy Part Number: 78-8027-0484-7 Rev: X

Release Date: Feb 13, 2002

3M / GTIS

Instructions / Rev

Sort By: loc_ref_id

ESD

Item Find	3M ID Number	Rev	Rls	Type	Part Description	Qty	Unit	Special Instructions
00000	78-8027-0484-7	X	Y		Press - 3640			
	78-8027-0484-7	X	Y	d	Assy - Press, 3640	1.0	EA	
FN001	78-8015-1154-0	G	Y	f	Assy - Handle, Left Hand	1.0	EA	
FN002	78-8005-0623-6	1	N	f	Handle - 3 3/16 Lg x 7/8 OD, with 3/8 Holes, Plastic, Blk	1.0	EA	
FN003	78-8015-1161-5	F	Y	f	Shaft - Handle	1.0	EA	
FN004	78-8004-5715-8	E	Y	f	Spacer - Handle	2.0	EA	
FN005	78-8015-1155-7	H	Y	f	Assy - Handle, Right Hand	1.0	EA	
FN006	18-9260-5800-1	1	N	f	Pin - Spring, Cyl. 3/32 x 5/8 Steel	2.0	EA	
FN007	78-8022-4232-7	F	Y	f	Spring - Barrel	1.0	EA	
FN008	78-8027-0485-4	K	Y	f	Assy - Adjustment	1.0	EA	
FN009	70-7023-8760-9	1	N	f	Washer - Flat, .312 ID x .50 OD x .031 THK, Nylon, Ni	8.0	EA	
FN010	78-8015-1165-6	G	Y	f	Stud - Pivot	2.0	EA	
FN011	78-8656-3965-8	1	N	f	Retaining Ring - Truarc 5100-31	6.0	EA	
FN012	78-8015-1156-5	H	Y	f	Assy - Link, Connecting	2.0	EA	
FN013	78-8015-1166-4	F	Y	f	Retainer - Pivot	2.0	EA	
FN015	78-8006-5362-4	G	Y	f	Stud - Press	2.0	EA	
FN016	78-8027-0486-2	E	Y	f	Label - 3640	1.0	EA	
FN017	78-8004-5713-3	J	Y	f	Frame - Press, Machining	1.0	EA	
FN020	78-8005-3091-3	1	N	f	Bearing - Oilite AA-710-4	1.0	EA	
FN022	26-1003-3721-6	1	N	f	Pin - Spring, 3/32 Dia x 3/4 Lg., Zinc/Black	2.0	EA	
FN024	78-8011-4530-7	B	Y	f	3442-9 Platen Assembly	1.0	EA	

Note: Component item revisions under column 'Rev' are for reference only and may change based on the date of the printout.

Type: a = Assembly, d = Document, f = Folder, p = Part, r = Reference, t = Tab Document.