



10% DETERGENT

CODE : C071

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830
Revision date: 15/03/2021 Version: 10.4

Generated : 15/03/2021

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form	: Mixture
Trade name	: 10% DETERGENT
UFI	: WUT2-J0DC-Y003-DUTE
Product code	: C071
Type of product	: Detergent

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Main use category	: Professional use
Industrial/Professional use spec	: For professional use only
Use of the substance/mixture	: Hand dishwashing detergent

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

SELDEN RESEARCH LIMITED

STADEN LANE
BUXTON
DERBYSHIRE
SK17 9RZ
UNITED KINGDOM

Tel: 01298 26226 Fax: 01298 26540
Email: safety@selden.co.uk

SELDEN EUROPE B.V.

WATERMOLEN 13
6229 PM
MAASTRICHT
NEDERLAND

Tel: 00 32 16 53 07 96
Email: info@selden.eu

1.4. Emergency telephone number

Mon to Fri 8.30am to 5.00pm - 01298 26226

Tel: 00 32 16 53 07 96

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Serious eye damage/eye irritation, Category 2 H319
Full text of H statements : see section 16

Adverse physicochemical, human health and environmental effects

Causes serious eye irritation.

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP)



GHS07

Signal word (CLP)	: Warning
Hazard statements (CLP)	: H319 - Causes serious eye irritation.
Precautionary statements (CLP)	: P264 - Wash hands thoroughly after handling. P280 - Wear eye protection. P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P337+P313 - If eye irritation persists: Get medical advice/attention.

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Benzenesulphonic acid, C10-13-alkyl derivs., sodium salts	(CAS-No.) 68411-30-3 (EC-No.) 270-115-0 (REACH-no) 01-2119489428-22	1 – 5	Acute Tox. 4 (Oral), H302 Skin Irrit. 2, H315 Eye Dam. 1, H318
Sodium laurylether sulphate	(CAS-No.) 68891-38-3 (EC-No.) 500-234-8 (REACH-no) 01-2119488639-16	1 – 5	Eye Dam. 1, H318 Skin Irrit. 2, H315
Amides, coco, compounds with diethanolamine	(CAS-No.) 68603-42-9 (EC-No.) 271-657-0 (REACH-no) 01-2119490100-53	1 – 5	Skin Irrit. 2, H315 Eye Dam. 1, H318

Specific concentration limits:

Name	Product identifier	Specific concentration limits
Sodium laurylether sulphate	(CAS-No.) 68891-38-3 (EC-No.) 500-234-8 (REACH-no) 01-2119488639-16	(5 ≤C < 10) Eye Irrit. 2, H319 (10 ≤C < 100) Eye Dam. 1, H318

Full text of H-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact	: Wash skin with plenty of water.
First-aid measures after eye contact	: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
First-aid measures after ingestion	: Get immediate medical advice/attention.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects after skin contact	: Repeated or prolonged skin contact may cause irritation.
Symptoms/effects after eye contact	: Eye irritation.
Symptoms/effects after ingestion	: May cause gastrointestinal irritation, nausea, vomiting and diarrhoea.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	: Water spray. Dry powder. Foam. Carbon dioxide.
------------------------------	--

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products in case of fire : Toxic fumes may be released.

5.3. Advice for firefighters

Protection during firefighting : Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

Emergency procedures : Ventilate spillage area. Avoid contact with skin and eyes.

6.1.2. For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Take up liquid spill into absorbent material.
Other information : Dispose of materials or solid residues at an authorized site.

6.4. Reference to other sections

For further information refer to section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Ensure good ventilation of the work station. Avoid contact with skin and eyes. Wear personal protective equipment.
Hygiene measures : Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Store in a well-ventilated place. Keep cool.

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1 National occupational exposure and biological limit values

No additional information available

8.1.2. Recommended monitoring procedures

No additional information available

8.1.3. Air contaminants formed

No additional information available

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

8.1.4. DNEL and PNEC

No additional information available

8.1.5. Control banding

No additional information available

8.2. Exposure controls

8.2.1. Appropriate engineering controls

Appropriate engineering controls:

Ensure good ventilation of the work station.

8.2.2. Personal protection equipment

8.2.2.1. Eye and face protection

Eye protection:

Safety glasses. EN 166

8.2.2.2. Skin protection

Skin and body protection:

Not required for normal conditions of use

Hand protection:

In case of repeated or prolonged contact wear gloves. Chemical resistant gloves (according to European standard EN 374 or equivalent)

Other skin protection

Materials for protective clothing:

Not required for normal conditions of use

8.2.2.3. Respiratory protection

Respiratory protection:

In case of insufficient ventilation, wear suitable respiratory equipment

8.2.2.4. Thermal hazards

No additional information available

8.2.3. Environmental exposure controls

Environmental exposure controls:

Avoid release to the environment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Appearance	: Mobile liquid.
Colour	: Green.
Odour	: odourless.
Odour threshold	: No data available
pH	: 5
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: Not applicable
Freezing point	: No data available
Boiling point	: $\geq 100\text{ }^{\circ}\text{C}$
Flash point	: No data available

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Not applicable
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: 1.01
Solubility	: Soluble in water.
Partition coefficient n-octanol/water (Log Pow)	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Stable under normal conditions of use.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

10.5. Incompatible materials

None under normal use.

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity (oral)	: Not classified
Acute toxicity (dermal)	: Not classified
Acute toxicity (inhalation)	: Not classified
Skin corrosion/irritation	: Not classified pH: 5
Serious eye damage/irritation	: Causes serious eye irritation. pH: 5
Respiratory or skin sensitisation	: Not classified
Germ cell mutagenicity	: Not classified
Carcinogenicity	: Not classified
Reproductive toxicity	: Not classified
STOT-single exposure	: Not classified
STOT-repeated exposure	: Not classified

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Aspiration hazard : Not classified

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general : The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.

Hazardous to the aquatic environment, short-term (acute) : Not classified

Hazardous to the aquatic environment, long-term (chronic) : Not classified

Benzenesulphonic acid, C10-13-alkyl derivs., sodium salts (68411-30-3)

LC50 - Fish [1]	1.67 mg/l
EC50 - Other aquatic organisms [1]	2.9 mg/l waterflea
EC50 - Other aquatic organisms [2]	127.9 mg/l

Amides, coco, compounds with diethanolamine (68603-42-9)

LC50 - Fish [1]	5.7 mg/l
EC50 - Other aquatic organisms [1]	1.2 mg/l waterflea
EC50 - Other aquatic organisms [2]	5.6 mg/l

12.2. Persistence and degradability

No additional information available

12.3. Bioaccumulative potential

Benzenesulphonic acid, C10-13-alkyl derivs., sodium salts (68411-30-3)

Partition coefficient n-octanol/water (Log Pow)	3.32
---	------

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

No additional information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.

SECTION 14: Transport information

In accordance with ADR / IMDG / IATA

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

14.1 UN number

UN-No. (ADR) : Not applicable
 UN-No. (IMDG) : Not applicable
 UN-No. (IATA) : Not applicable

14.2. UN proper shipping name

Proper Shipping Name (ADR) : Not applicable
 Proper Shipping Name (IMDG) : Not applicable
 Proper Shipping Name (IATA) : Not applicable

14.3. Transport hazard class(es)

ADR
 Transport hazard class(es) (ADR) : Not applicable
IMDG
 Transport hazard class(es) (IMDG) : Not applicable
IATA
 Transport hazard class(es) (IATA) : Not applicable

14.4. Packing group

Packing group (ADR) : Not applicable
 Packing group (IMDG) : Not applicable
 Packing group (IATA) : Not applicable

14.5. Environmental hazards

Dangerous for the environment : No
 Marine pollutant : No
 Other information : No supplementary information available

14.6. Special precautions for user

Overland transport

Not applicable

Transport by sea

Not applicable

Air transport

Not applicable

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

Detergent Regulation (648/2004/EC): Labelling of contents:	
Component	%
anionic surfactants	5-15%
non-ionic surfactants	<5%

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SODIUM BENZOATE	
-----------------	--

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Full text of H- and EUH-statements:

Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4
Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Skin Irrit. 2	Skin corrosion/irritation, Category 2
H302	Harmful if swallowed.
H315	Causes skin irritation.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.

Classification and procedure used to derive the classification for mixtures according to Regulation (EC) 1272/2008 [CLP]:

Eye Irrit. 2	H319	Bridging principle "Substantially similar mixtures"
--------------	------	---

Safety Data Sheet (SDS), EU

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.