

Cement Shear LXT®

DJS800

18V • 13 mm • 0 – 3 000 min⁻¹

Powerful cement fiber shear with 13 mm cutting capacity

A 18V LXT® battery powered brushless cement shear with 13 mm cutting capacity. Adjustable speed between 0 – 3 000 min⁻¹. Head is adjustable by 360° for increased cutting convenience. LED light for illuminating work area and lock-on button for continuous operation.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Strokes per Minute (SPM)	0 - 3000 min ⁻¹
Tool weight with battery	2,1 - 2,5 kg
Product Dimensions (L x W x H):	379 x 79 x 216 mm
Brushless Motor	✓
Max Cutting Capacity	13 mm
Vibration Level, Cutting Hardie Board	6,0 m/s ²
Vibration Uncertainty (K Factor), Cutting Hardie Board	1,5 m/s ²

User benefits

- Brushless maintenance-free and long-life motor
- 360° swivel shear head for increased cutting convenience
- Built-in LED light with afterglow function illuminates the work area
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Ergonomic soft grip handle provides increased comfort
- Lock-on feature for continuous operation
- Battery protection circuit protects against overloading, over-discharging and over-heating



Related products

Other

User manual

Parts drawing