Baumer
Passion for Sensors

Temperature sensor

PT55H

Article number: 96004370

Overview

- Precision measurement from -50 ... 250 °C
- Integrated 4 ... 20 mA transmitter with high accuracy
- Compact housing with touch screen
- Convenient installation and easy operation
- IO-Link Dual Channel for easy commissioning
- In addition to the standard lengths, custom lengths up to 3000 mm are available on request



Picture similar

Technical data

Performance characteristics	
Pt100 accuracy class (EN 60751)	1/1 B ± (0.3 + 0.005 × t)°C 1/1 A ± (0,15 + 0,002 × t)°C 1/3 B ± 1/3 × (0.3 + 0.005 × t)°C 1/6 B ± 1/6 × (0.3 + 0.005 × t)°C
Max. measuring error	± 0.06 % FSR @ 25 °C Including zero-point and span error, non-linearity (by terminal base line), hysteresis and non-repeatability (EN 61298-2)
Thermal response time, T50	RTD element and transmitter combined < 2.5 s , Ø4 mm < 6.5 s , Ø6 mm < 10.5 s , Ø8 mm
Temperature coefficient	< 0.025 K/K Factor of change in ambient temperature from 25°C
Process temperature	Refer to section "Operating conditions"
Process conditions	
Process temperature	-50 … 125 °C , without cooling neck -50 … 250 °C , with cooling neck
SIP/CIP compatibility	< 30 min, without cooling neck @ medium temperature up to 150 °C
Process connection	
Connection variants	Refer to section "Dimensional drawings"
Sensor length	Refer to section "Ordering information" Other lengths ≤ 3000 mm on request
Sensor diameter outside	ø 6 mm ø 8 mm
Mounting position	Any, top, bottom, side
Standard response tip	ø 6 mm ø 8 mm
Fast response tip	ø 4 mm
Sensor tube material	AISI 316L (1.4404)

Process connection	
Surface roughness wetted parts	Ra ≤ 0.8 µm Ra ≤ 0.8 µm, electropolished, optional Ra ≤ 0.4 µm, optional Ra ≤ 0.4 µm, electropolished, optional
Ambient conditions	
Operating temperature range	-30 … 70 °C , with display -10 … 70 °C , optimal display readability
Storage temperature range	-40 … 85 °C
Degree of protection (EN 60529)	IP67 IP69K , with appropriate mating connector
Humidity	≤ 100 % RH , condensing
Vibration (sinusoidal) (EN 60068-2-6)	1.6 mm p-p (2 … 25 Hz), 4 g (25 … 100 Hz), 1 octave / min.
Shock (EN 61373)	300m/s² @ 15ms
Housing	
Style	Compact transmitter, Ø50 mm
Overall size	Refer to section "Dimensional drawings"
Material	AISI 304 (1.4301)
Electrical connection	
Connector	M12-A, 4-pin, stainless steel
Power supply	
Voltage supply range	15 … 35 V DC 18 … 30 V DC , with IO-Link
Power-up time	< 1500 ms @ 24 V
Current consumption (no load)	3.5 mA … 23 mA , 2-wire 16 mA typ., 25 mA max., 3-wire mode
Reverse polarity protection	Yes

2026-02-16 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.

Temperature sensor

PT55H

Article number: 96004370

Technical data

Compliance and approvals

EMC	EN 61326-1 EN 61326-2-3 Deviation during immunity testing ≤ 0.2% FSR

Compliance and approvals

Hygiene	3-A (74-07) EHEDG EL Class I

Output signals

Switching output

Output type	PNP NPN Digital (push-pull)
Switching logic	High-Active Low-Active
Voltage drop	< 2 V, switching output
Current rating	100 mA , max.
Off leak current	< 160 µA , max.
Damping	0 … 60 s , programmable

4 ... 20 mA

Accuracy	± 0.05 % FSR
Step response time, T90	< 25 ms
Load resistance	Rs ≤ (V DC - 15 V)/23 mA, 2-wire mode Rs ≤ (V DC - 10 V)/23 mA, 3- & 4-wire mode
Temperature drift (by ambient)	< 0.1 % FSR/K (± 1.6 µA/K) Factor of change in ambient temperature from 25°C
Ripple immunity	< 1 % FSR (1 Vrms, 50Hz...1kHz)
Effect of variations in supply voltage	< 0.01 % FSR/V (± 1.6 µA/V), deviating from 24 VDC
Damping	0 … 60 s , programmable

IO-Link interface

IO-Link version	1.1
Device profile	Smart Sensor Profile
IO-Link port type	Class A
Baud rate	38,4 kbaud (COM2)
Cycle time	≥ 14 ms
Process data length	48 bit
SIO-mode	Yes
Process data (cyclic)	Process temperature Switch state State of alert
Diagnostic data (acyclic)	CPU temperature Operation
Adjustable data (acyclic)	Switch parameters Current output limit values Display configuration Tags Password for access
Dual Channel	IO-Link / SIO Mode
Dual Channel 2	Analogue / SIO Mode

2026-02-16 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.

PT55H

Article number: 96004370

Display

User configurable data


Error- / Warning-indication	Individually configurable display and backlight indication in white, green or red colour, steady or flashing light. Configurable limits over the range
Measuring unit	°C °F K

General information

Panel type	Graphical LCD
Display range	-9999 … 99999
Max. digit height	21.8 mm
Material	Polycarbonate

Operating conditions

Ordering key	Process connection	BCID	Process pressure (bar)	Continuous Process temperature Standard @ Tamb ≤ 20 °C (° C)	Process temperature with cooling neck @ Tamb ≤ 20 °C (° C)
A020	M12 × 1.5 hygienic	A02	-1 … 40	-50 … 125	-50 … 250
A030	G 1/2 A hygienic	A03	-1 … 40	-50 … 125	-50 … 250
B010	BHC 3A DN 38	B01	-1 … 40	-50 … 125	-50 … 250
C040	ISO 2852 (Tri-Clamp), DN 33.7; 38, Ø 50.5	C04	-1 … 40	-50 … 125	-50 … 250
V020	Varivent type N, Ø 68	V02	-1 … 16	-50 … 125	-50 … 250



2026-02-16 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.


Temperature sensor


PT55H


Article number: 96004370


Dimensional drawings (mm)

Housing











Cooling neck


Process connection



M12 × 1.5 hygienic (BCID: A02)



G 1/2 A hygienic (BCID: A03)



BHC 3A DN 38 (BCID: B01)
3-A / EHEDG certified

2026-02-16 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.


Temperature sensor

PT55H


Article number: 96004370

Dimensional drawings (mm)


Process connection




Tri-Clamp Ø 50.5 (BCID: C04),
3-A / EHEDG certified



Varivent® DN 32 … 125; 1 1/2" … 6" (Type N),
Ø 68 (BCID: V02),
3-A / EHEDG certified





Standard response tip



Fast response tip

Electrical connection

Equivalent circuit	Function	Pin assignment
	+Vs	1
	Iout / SW2	2
	GND (0 V)	3
	IO-Link / SW1	4
	Frame Ground	Plug thread

Coding	Operating mode	Used pins
	IO-Link / dual channel	1, 2, 3, 4
	analog 3-wire	1, 2, 3
	analog 2-wire	1, 2

Ordering information

Ordering key - Configuration possibilities see website

	PT55H	**-**	**####**	**.**	**#**	**#**	**#**	**#**	**#**	**2**	**2**	**1**	**.**	**2**	**#**	**0**	**0**	**0**	**#**	**#**	**####**
Product																					
	PT55H																				

2026-02-16 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.

Temperature sensor

PT55H

Article number: 96004370

Ordering information

Ordering key - Configuration possibilities see website

	PT55H	-	####	.	#	#	#	#	#	2	2	1	.	2	#	0	0	0	#	#	####
Process connection																					
M12 x 1.5 hygienic (A02)[1]			A020																		
G 1/2 A hygienic (A03)[1]			A030																		
BHC 3A DN38 (B01)			B010																		
ISO 2852 (Tri-Clamp) DN38 (C04)			C040																		
Varivent® DN 32...125; 1 1/2...6 (Type N), Ø 68 (V02)			V020																		
Sensor tip																					
Rod 6 mm, tip 6 mm					1																
Rod 6 mm, tip 4 mm					2																
Rod 8 mm, tip 8 mm					3																
Rod 8 mm, tip 4 mm					4																
Sensor element																					
Pt100 1/1 B EN 60751, single, 2-wire						1															
Pt100 1/3 B EN 60751, single, 2-wire						3															
Pt100 1/6 B EN 60751, single, 2-wire						5															
Pt100 1/1 A EN 60751, single, 2-wire						7															
Pt100 1/1 B EN 60751, single, 4-wire						A															
Pt100 1/3 B EN 60751, single, 4-wire						B															
Pt100 1/6 B EN 60751, single, 4-wire						C															
Pt100 1/1 A EN 60751, single, 4-wire						D															
Cooling neck																					
Without cooling neck							0														
With cooling neck							4														
Process temperature																					
-50...125°C								1													
-50...250°C								3													
Max. process pressure																					
40 bar									2												
100 bar									3												
Interface																					
IO-Link Dual Channel, 4...20 m										2											
Electrical connection																					
M12-A, 4 pin, stainless steel, with integrated transmitter											2										
Display																					
With display												1									
Wetted parts material																					
AISI 316L (1.4404)														2							
Surface roughness																					
Ra ≤ 0.8 µm															1						
Ra ≤ 0.4 µm															2						
Electropolished, Ra ≤ 0,8 µm															3						
Electropolished, Ra ≤ 0,4 µm															4						
Gasket material																					
Without																0					
Explosion protection																					
Without																	0				
Industrial approvals																					
Standard																		0			

2026-02-16 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.

Temperature sensor

PT55H

Article number: 96004370

Ordering information

Ordering key - Configuration possibilities see website

	PT55H	-	####	.	#	#	#	#	#	2	2	1	.	2	#	0	0	0	#	#	####
Special approvals																					
Standard																			0		
3-A / EHEDG																			3		
Configuration																					
Factory settings																				0	
Customer-specific																				1	
Sensor tube length (mm)																					
20																					0020
30																					0030
50																					0050
100																					0100
150																					0150
200																					0200
300																					0300
Customer lengths on request [20 - 3000]																					####

(1) Without 3A / EHEDG

2026-02-16 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.