

Finishing Sander LXT®

DBO480

18V • 112 x 102 mm

LXT® Battery powered Finishing Sander for demanding use.

Hook & Loop type abrasive paper can be used on this Sander. Compact and lightweight structure and conveniently located on/off switch for easy one handed operation.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Orbits per Minute	11000 - 14000 min ⁻¹
Sanding Orbit Diameter	1,5 mm
Sound Pressure Level (L _{pA})	75 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,4 - 1,7 kg
Product Dimensions (L x W x H):	171 x 112 x 152 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Strokes per Minute (SPM)	22000 / 28000 min ⁻¹
Vibrations per minute	11000 / 14000 min ⁻¹
Sanding Pad Dimensions	112 x 102 mm
Dimensions of Clamped Abrasive Sheet	114 x 140 mm

User benefits

- Hook & loop type abrasive paper can be used
- Compatible with various pads
- Large clamping lever for quick and easy paper installation

Link to product - www.makitauk.com



Related products

■ Optional AC

191Y24-8
Base Plate



■ Other

User manual

Parts drawing