



Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Cable Connectors



Connector System: **Wire-to-Board**

Number of Positions: **34**

Centerline (Pitch): **2.54 mm [.1 in]**

PCB Mount Retention: **Without**

PCB Mount Orientation: **Vertical**

Features

Product Type Features

Connector Product Type	Connector Assembly
Ribbon Cable Connector Header Type	Pin Header
Connector System	Wire-to-Board
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	34
PCB Mount Orientation	Vertical
Number of Rows	2

Electrical Characteristics

Operating Voltage	250 VAC
Insulation Resistance	5000 MΩ

Body Features

Daisy Chain	Without
Primary Product Color	Black
Connector Profile	Low

Contact Features

Contact Underplating Material	Nickel
-------------------------------	--------



Mating Pin Diameter	.64 mm[.025 in]
Contact Mating Area Plating Material Thickness	.76 μm[29.92 μin]
Wire Contact Termination Area Plating Material	Tin
Mating Square Post Dimension	.64 mm[.025 in]
Contact Shape & Form	Tuning Fork
Contact Mating Area Plating Material	Gold (Au), Gold Flash over Palladium Nickel
Contact Base Material	Phosphor Bronze
Wire Contact Termination Area Plating Thickness	1.27 μm[50 μin]
Contact Type	Socket
Contact Current Rating (Max)	1 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Panel Mount Feature	Without
Mating Alignment	With
PCB Mount Alignment	Without
PCB Mount Retention	Without
Mating Alignment Type	Polarization
Mating Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Thermoplastic
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Compatible Insulation Diameter Range	.79 – .94 mm[.031 – .037 in]
Connector Width	7.49 mm[.295 in]
Wire Size	28 – 26 AWG
Connector Height	15.16 mm[.597 in]
Connector Length	47.75 mm[1.88 in]
Row-to-Row Spacing	2.54 mm[.1 in]

Usage Conditions

--	--



Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
UL Rating	Recognized
UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	CSA LR7189, UL E28476

Packaging Features

Packaging Quantity	50
Packaging Method	Box & Tube, Tube

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 2-111446-2 034 UNIV I/O 30DP NO EARS	 TE Part # 5111448-8 034 UNIV I/O 30DP SLOT	 TE Part # 768340-1 UNIV HAND TOOL KIT AMPLATCH	 TE Part # 5088450-8 PULL LOOP, CUT LENGTH 1.58 IN
 TE Part # 5103311-7 A/L LOW PRO HDR 34P RA BLACK	 TE Part # CAT-AM74-UN384H AMP-LATCH UNIVERSAL HEADERS	 TE Part # 5103310-7 A/L LOW PRO HDR 34P RA BLACK	 TE Part # 5103309-7 A/L LOW PRO HDR 34P VERT BLACK
 TE Part # 5104340-7 A/L LOW PRO HDR 34P RA HT	 TE Part # 2-111494-1 034 UNIV I/O 30DP SLOT LTCH	 TE Part # 5103308-7 A/L LOW PRO HDR 34P VERT BLACK	 TE Part # 499252-6 034 STRAIN RELIEF A-L RCPT
 TE Part # 5104338-7 A/L LOW PRO HDR 34P VERT HT	 TE Part # 2-111492-2 034 UNIV I/O 30DP NO EARS LTCH		

Also in the Series | AMP-LATCH - NOVO



Ribbon Cable Connectors(46)



Customers Also Bought

TE Part #5102160-4
A/L UNIV HDR 20P RA

TE Part #1-1617121-1
JMAC-26XP = M39016/9-062P

TE Part #103946-1
8X2 MTE SHRD PIN SR POL .100CL

TE Part #1-208778-0
AMPLIMITE,SKT CONT,SZ 20

TE Part #251379-000
SO63-3-55-24-90

TE Part #6609108-5
PE0S0DZXC M0=C7043

TE Part #2000713-4
RA Keyed Guide Mod, Vita 46, Machined

TE Part #530721-1
MINI BOX EXTERNAL KEY PASSIV

TE Part #207684-4
AMPLIMITE,SKT CONT,SZ 22

TE Part #9-1393222-1
V23061B1005A301=MINISTARKSTROM

Documents

Product Drawings

034 NOVO DUAL 30DP FT

English

CAD Files

Customer View Model

ENG_CVM_CVM_1658624-8_D.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1658624-8_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1658624-8_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages
Ribbon Cable Interconnect Solutions

English

Product Specifications
Application Specification

English

Instruction Sheets
Instruction Sheet (U.S.)

English

Agency Approvals
Agency Approval Document

English