

DCD708N-XJ

18V XR Brushless Compact Drill Driver - Naked Unit

The DEWALT brushless drill driver delivers 65Nm of torque in a 160mm long body for improved performance and runtime in the tightest spaces. Other features include a 2 speed all metal transmission, 15 torque settings for increased versatility in applications and a bright LED on the base of the tool for enhanced visibility.

Selling Propositions

- Only 160mm in length, allowing you to get into even smaller spaces
- Only 1.1kg (tool only) for ultimate portability and ease of use
- Efficient brushless motor delivers high performance, extends tool life and allows for a much shorter design.
 - · Foot LED with delay feature for better workpiece illumination
 - 65Nm torque allows you to achieve tough applications
- 15 Position adjustable torque control for consistent screw driving into a variety of materials with different screw sizes

Standard Equipment

· Belt hook

Warranty specifications

 Dewalt European Warranty 3 years (subject to registration)

Specifications	
Max. Cutting Capacity (Wood)	30.0mm
Max. Cutting Capacity (Metal)	13.0mm
No Load Speed	0-450/0-1650 rpm
Max Torque (Hard)	65.0Nm
No. of Speeds	2
Max Torque (Soft)	26.0Nm
Chuck Capacity	13mm
Weight	1.1kg
Length	160.0mm
Height	201.0mm
Sound Pressure	73.0dB(A)
Sound Pressure Uncertainty	3.0dB(A)
Hand/Arm Vibration - Drilling into Metal	<2.5m/s²
Uncertainty K1 (Vibration)	1.5m/s²
Hand/Arm Vibration - Screw Driving without Impact	<2.5m/s²
Uncertainty K2 (Vibration)	1.5m/s²
Nominal maximum RPM	0-450/0-1650
Maximum drilling diameter (steel)	30
Maximum drilling diameter (wood)	13
Torque	65
Maximum clamping range of drill head	13
Minimum clamping range drill head	1.5