


FEATURES

- **660 lm Luminous Flux:** Provides bright and clear illumination for detailed inspections
- **IP66 Rating:** Offers protection against dust and powerful water jets, suitable for harsh environments
- **3.7 V Lithium-ion Battery:** Ensures long-lasting power with a capacity of 3350 mAh
- **8.5 Hours Runtime:** Allows for extended use without frequent recharging
- **Polycarbonate and TPE Housing:** Durable construction for enhanced impact resistance
- **Micro USB Plug Type:** Convenient and widely compatible charging option
- **LED Light Style:** Energy-efficient lighting with a long lifespan

RS PRO 660 lm LED Inspection Lamp, 3350 mAh Battery

RS Stock No: 655-946



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO LED Inspection Lamp is designed for professionals who require reliable and efficient lighting in challenging environments. With a robust polycarbonate and TPE housing, this lamp is ideal for use in industrial settings, providing bright illumination with its 660-lumen output. Its rechargeable 3350 mAh lithium-ion battery ensures long-lasting performance, making it a practical choice for extended tasks.

General Specifications

Colour	Red
Lamp Supplied	Yes
Light Style	LED
Luminous Flux	660 lm
Product Type	Inspection Lamp
Run Time	8.5 h
Wireless Charging	No

Electrical Specifications

Battery Capacity	3350 mAh
Battery Type	3.7 V Lithium-ion
Plug Type	Micro USB
Rechargeable	Yes
Voltage	5 V dc

Mechanical Specifications

Housing Material	Polycarbonate, TPE
Length	32.3 mm

Protection Category

IP Rating	IP66
-----------	------

Approvals

Standards/Approvals	CE
---------------------	----