## **SIEMENS**

Product data sheet 3LD2264-1GP53



EMERG. STOP SWITCH 3-POLE IU=32, P/AC-23A AT 400V=11.5KW 1NO+1NC, 1 N-TERMINAL INSULATION-ENCLOSED, IP65 ROTARY ACTUATOR RED/YELLOW (EMERG. STOP) METRIC SCREW CONNECTION

Similar to image

General technical details:				
Product brand name		SENTRON		
product designation		main and EMERGENCY-OFF switches		
Type from device		fixed mounting		
Design of the operating mechanism		rotary actuator, red/yellow		
Protection class IP		IP65		
Number of poles		3		
Acceptability for application				
• switch disconnector		Yes		
• main switch		Yes		
safety cut-out switch		Yes		
emergency stop switch		Yes		
maintenance/repair switch		Yes		
Product equipment / interlock		Yes		
Type of the driving mechanism / motor drive		No		
Product extension / optional				
• motor drive		No		
voltage trigger		No		
Ambient temperature / during operating	°C	-25 +55		

Insulation voltage / rated value	V	690
Impulse voltage resistance / rated value	V	6,000
Active power loss / per conductor / typical	W	1.8
Mechanical operating cycles as operating time / of the main contacts / typical		100,000
Protection against electrical shock		finger-safe
Item designation / according to DIN EN 61346-2		S
Item designation / according to DIN 40719 extendable after IEC 204-2 / according to IEC 750		S
Main circuit:		
Continuous current / rated value	А	32
Operating current / at AC-21 / rated value	Α	32
Short-time current resistance (lcw) / at 690 V / limited to 1 s / rated value	Α	640
Operating frequency	Hz	50 60
Operating voltage / at 50/60 Hz / for AC / rated value	V	690
Service power / at AC-3		
• at 400 V / rated value	kW	9.5
• at 690 V / rated value	kW	9.5
Service power / at AC-23 A		
• at 400 V / rated value	kW	11.5
at 690 V / rated value	kW	11.5
Operating cycles / maximum	1/h	50
Auxiliary circuit:		
Number of NC contacts / for auxiliary contacts		1
Number of NO contacts / for auxiliary contacts		1
Number of change-over switches / for auxiliary contacts		0
Continuous current / of the auxiliary contact / rated value	Α	10
Operating voltage / of the auxiliary contacts / for AC / maximum	V	500
Insulation voltage / of the auxiliary switch / rated value	V	500
Short-circuit:		
Design of the fuse link / for short-circuit protection of the main circuit / necessary		fuse gL/gG: 40 A
Design of the fuse link / for short-circuit protection of the auxiliary switch / required		fuse gL/gG: 10 A
Installation/mounting/dimensions:		
Type of mounting		floor mounting
• front mounting		No

	No
	No
	No
mm	100
mm	152
mm	117
	mm

Connection type:	
Design of the electrical connection / for main current circuit	connection terminals
Design of the electrical connection / for auxiliary contact	connection terminals
Type of the connectable conductor cross-section / for main contacts	
• solid	1.5 16 mm2
finely stranded / with conductor end processing	10 mm²
• stranded	1.5 16 mm2
Type of connectable conductor cross section / for auxiliary contacts	
• solid	2x (0.75 to 2.5 mm2), 1x 4 mm2
• stranded	2x (0.75 2.5 mm2), 1x 4 mm2

Certificates/approvals:		
Verification of suitability		CSA / UL / CCC
Conductor cross section that can be connected / for main contacts / solid / minimum	mm²	1.5
Conductor cross section that can be connected / for main contacts / solid / maximum	mm²	16
Conductor cross section that can be connected / for main contacts / stranded / minimum	mm²	1.5
Conductor cross section that can be connected / for main contacts / stranded / maximum	mm²	16
Conductor cross-section that can be connected / for main contacts / stranded wire / with conductor end processing / maximum	mm²	10
Conductor cross section that can be connected / for auxiliary contacts / solid / minimum	mm²	0.75
Conductor cross section that can be connected / for auxiliary contacts / solid / maximum	mm²	4
Conductor cross-section that can be connected / for auxiliary contact / stranded wire / with conductor end processing / minimum	mm²	0.75
Conductor cross-section that can be connected / for auxiliary contact / stranded wire / with conductor end processing / maximum	mm²	2.5
Conductor cross section that can be connected / for auxiliary contacts / stranded / min.	mm²	0.75

Conductor cross section that can be connected / for auxiliary contacts / stranded / max.

mm²

4

## Certificates/approvals:

**General Product Approval** 

**Test Certificates** 



ROSTEST



Manufacturer other

**Shipping Approval** 

other





GL



Manufacturer

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

http://www.siemens.com/lowvoltage/catalogs

Industry Mall (Online ordering system)

http://www.siemens.com/lowvoltage/mall

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


http://support.automation.siemens.com/WW/view/en/3LD2264-1GP53/all


 $Image\ database\ (product\ images,\ 2D\ dimension\ drawings,\ 3D\ models,\ device\ circuit\ diagrams,\ ...)$ 


http://www.automation.siemens.com/bilddb/cax\_en.aspx?mlfb=3LD2264-1GP53


**CAx-Online-Generator** 

http://www.siemens.com/cax









Dec 12, 2011 last change: