

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Random Orbit Sander

PRO GET 75-150



150mm turbo sander with outstanding control

The most important data

Rated input power	750 W
Sanding pad diameter	150 mm
Orbit diameter	4.5 mm

Part Number 0 601 257 170

Technical data

Technical data

Sanding pad diameter	150 mm
No-load speed	3,300 – 7,300 rpm
Orbital stroke rate	6,600 – 14,600 opm
Sanding pad speed	290 – 640 rpm
Eccentricity	2.25 mm
Sanding sheet / disc attachment	Hook-and-loop fastening
Rated input power	750 W
Weight	2.6 kg
Orbit diameter	4.5 mm
Packaging dimensions (width x length x height)	160 x 406 x 154 mm
Voltage, electrical	240 V

Noise/vibration information

Sanding solid wood

Vibration emission value ah	6.5 m/s ²
Uncertainty K	1.5 m/s ²




Product data sheet

Power tools for trade & industry

Advantages:

- Perfectly designed ergonomic palm rest and handle with gripping circumference of only 18 cm provide best tool control
- Multi-hole sanding pad for sanding sheets with different hole pattern and for significantly increased dust extraction
- Extremely powerful 750 Watt motor and direct driven pad rotation deliver up to 45% higher removal rate



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

