


06130025

RCK 13 - Self centring

2D Technical Drawing

Dynamic 3D View
Technical Specifications

Part number (CODE)	06130025
Ød (DD) mm	25
ØD (D) mm	50
L1 (L1) mm	17
L2 (L2) mm	22
L3 (L3) mm	28
L (L) mm	34
Maximum torque Mt (MT) Nm	560
Clamping pressure - Shaft (CPS) N/mm ²	285
Clamping pressure - Hub (CPH) N/mm ²	140
Clamping screws DIN 912 MAT. 12.9 - Num. (CSN)	6
Clamping screws DIN 912 MAT. 12.9 - Type (CST)	M6x20
Clamping screws DIN 912 MAT. 12.9 - Torque (CSTQ) Nm	14
Extraction thread - Type (ETT)	M6
Extraction thread - Num. (ETN)	3
Weight (WEIGHT) kg	0.30